

208/240V Single Phase Whip in 5 ft. (1.52 m) length with L6-30R for Breakered 3-Phase Distribution Cabinets

MODEL NUMBER: **SUWL630C-5**



Highlights

- 208/240V single phase whip distribution cabinet accessory
- 5-ft. (1.52 m) length with 3-ft. (0.91 m) removed outer jacket
- 3 conductor 10AWG stranded wire
- L6-30R outlet (208/240V 30A)

Description

208/240V single phase whip with L6-30R outlet distributes power from 3 phase distribution cabinet to critical equipment racks. 5-ft. (1.52 m) insulated and 3-ft. (0.91 m) of removed outer jacket cabling supports hardwire connection to SUBB230 circuit breaker in SUDC208V series 3 phase distribution racks. L6-30R outlet is compatible with 208/240V loads and Power Distribution Units (PDUs) supporting a L6-30P plug-in connection.

Features

- 208/240V single phase whip with L6-30R outlet
- Distributes power from 3 phase distribution cabinet to critical equipment racks
- 5-ft. (1.52 m) insulated and 3-ft. (0.91 m) of removed outer jacket cabling supports hardwire connection to SUBB230 circuit breaker in SUDC208V series 3 phase distribution racks
- L6-30R outlet is compatible with 208/240V loads and Power Distribution Units (PDUs) supporting a L6-30P plug-in connection

Specifications

OVERVIEW	
UPC Code	037332156174
INPUT	
Input Connection Type	Hardwire (3 wire - L, N, G)



Tripp Lite
 1111 W. 35th Street
 Chicago, IL 60609 USA
 Telephone: 773.869.1234
www.tripplite.com

OUTPUT	
PDU Recommendation Notes	Compatible with all PDU brands fitted with a L6-30P (30A 208/240V) input plug, including Tripp Lite PDU1230 ; PDUV30HV ; PDUMH30HV ; PDUMV30HV ; PDUMNH30 ; PDUMH30HV19NET ; PDUMH30HVNET ; and PDUMH30HVNET
Output Receptacles	(1) L6-30R
PHYSICAL	
Color	Black
Cable Length (ft.)	5
Cable Length (m)	1.52
Shipping Dimensions (hwd / cm)	16.26 x 30.48 x 30.48
Shipping Dimensions (hwd / in.)	6.40 x 12.00 x 12.00
Shipping Weight (kg)	1.32
Shipping Weight (lbs.)	2.90
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>