

Hot-Swappable Power Module, 30kVA/30kW for 220/380V 230/400V or 240/415V SVX Series UPS Systems

MODEL NUMBER: **SVX30PM**



Hot-swappable power module increases the output capacity of your Tripp Lite SVX Series UPS system by 30kVA 30kW to keep up with your data center's growing network infrastructure.

Description

The SVX30PM SmartOnline® Hot-Swappable Power Module mounts in your Tripp Lite SVX Series UPS system to help you meet the needs of your growing IT infrastructure. Configurable for additional output capacity or N+1 redundancy, the SVX30PM is rated at unity 1.0 power factor for maximum power to the connected load. You can remove or replace the hot-swap module without powering down equipment or hiring technicians, which maximizes uptime, simplifies maintenance and reduces service expenses. It fits into the equivalent of 3U of rack space in your UPS system for exceptional power density.

Compatible with Tripp Lite SVX Series models SVX30KL, SVX60KL, SVX90KL, SVX120KL, SVX150KL, SVX180KL, SVX210KL7P, SVX210KL8P (Large Frame), SVX30KM1P2B, SVX30KM1P3B, SVX30KM1P4B, SVX30KM1P5B, SVX60KM2P3B, SVX60KM2P4B, SVX60KM2P5B, SVX90KM3P5B (Medium Frame), SVX30KS1P2B, SVX30KS1P3B, SVX60KS2P3B, SVX90KS3P (Small Frame).

Features

Hot-Swap Power Module Increases Your UPS System's Capacity by 30kVA 30kW

- Configurable for additional capacity or N+1 redundancy
- Supports hot-swap installation and replacement
- Rated at unity 1.0 power factor for max power to connected load
- Occupies the equivalent of 3U of rack space in UPS system

Compatible with Tripp Lite SVX Series UPS Systems

- Large Frame: SVX30KL, SVX60KL, SVX90KL, SVX120KL, SVX150KL, SVX180KL, SVX210KL7P,

Highlights

- Compatible with 220/380V 230/400V 240/415V SVX Series UPS systems
- Configurable for additional capacity or N+1 redundancy
- Supports hot-swap installation and replacement
- Rated at unity 1.0 power factor for max power to connected load
- Occupies the equivalent of 3U of rack space in UPS system

Package Includes

- SVX30PM SmartOnline Hot-Swappable Power Module, 30kVA/30kW



SVX210KL8P

- Medium Frame: SVX30KM1P2B, SVX30KM1P3B, SVX30KM1P4B, SVX30KM1P5B, SVX60KM2P3B, SVX60KM2P4B, SVX60KM2P5B, SVX90KM3P5B
- Small Frame: SVX30KS1P2B, SVX30KS1P3B, SVX60KS2P3B, SVX90KS3P

Specifications

OVERVIEW	
UPC Code	037332198433
INPUT	
Nominal Input Voltage(s) Supported	220/380V 3-PH Wye; 230/400V 3-PH Wye; 240/415V 3-PH Wye
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Nominal Voltage	220/380V 3-PH Wye; 230/400V 3-PH Wye; 240/415V 3-PH Wye
PHYSICAL	
Shipping Dimensions (hwd / cm)	24.99 x 57.99 x 87.00
Shipping Dimensions (hwd / in.)	9.84 x 22.83 x 34.25
Shipping Weight (kg)	38.10
Shipping Weight (lbs.)	84.00
Unit Dimensions (hwd / cm)	13 x 49 x 73,63
Unit Dimensions (hwd / in.)	5.12 x 19.29 x 28.99
Unit Weight (kg)	34.52
Unit Weight (lbs.)	76.1
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>