


USB 2.0 Panel Mount Cable, 5-Pin Motherboard IDC to USB-A (F/F), 1 ft.

MODEL NUMBER: **U024-001-5P-PM**



Connects your computer's motherboard to a panel-mounted USB-A port that can be installed in a computer, booth, kiosk or podium.

Description

The U024-001-5P-PM USB 2.0 Hi-Speed Panel Mount Cable connects to a computer's motherboard to add a panel-mounted USB Type-A port. In addition to the front panel of a computer, the USB-A port can be installed in a trade show booth, retail kiosk or teacher's or lecturer's podium, allowing you to conveniently connect a thumb drive or other USB device. The PCB header terminates on almost any five-pin motherboard.

The one-foot cable supports data transfer rates up to 480 Mbps and is backward compatible with previous USB generations. Gold-plated contacts resist corrosion and ensure optimal signal transfer. Premium double-shielded cables with aluminum braid and aluminum Mylar foil feature twisted 28 AWG data lines and 24 AWG power lines. PVC jacket with molded connectors and integral strain relief provides durability and long life. Mounting screws included.

Features

Adds a Panel-Mounted USB-A Port Allows convenient USB access from a trade show booth, retail kiosk or lecturer's podium
5-pin PCB header terminates on computer's motherboard
 Supports data transfer speeds up to 480 Mbps
 Backward compatible with previous USB generations

Premium Construction for Premium Performance Corrosion-resistant gold-plated contacts for optimal signal transfer
 Fully molded construction with strain relief for durability and long life
 Flexible PVC jacket easy to install in tight spaces
 Double shielding with aluminum braid, aluminum Mylar foil and twisted 28/24 AWG data/power lines
 Mounting screws included

Specifications

OVERVIEW	
UPC Code	037332191106
INPUT	

Highlights

- Supports data transfer speeds up to 480 Mbps
- 5-pin PCB header connects to computer's motherboard
- USB-A port attaches with included screws
- Corrosion-resistant gold-plated contacts
- Backward compatible with previous USB generations

System Requirements

- Computer with 5-pin motherboard connector

Package Includes

- U024-001-5P-PM USB 2.0 Hi-Speed Panel Mount Cable, 1 ft.
- (2) Mounting screws



Cable Length (ft.)	1
Cable Length (m)	0.3
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	17.78 x 22.86 x 1.27
Shipping Dimensions (hwd / in.)	7.00 x 9.00 x 0.50
Shipping Weight (kg)	0.04
Shipping Weight (lbs.)	0.08
CONNECTIONS	
Side A - Connector 1	5 PIN IDC (FEMALE)
Side B - Connector 1	USB A (FEMALE)
FEATURES & SPECIFICATIONS	
Technology	USB 2.0 (High Speed); USB
STANDARDS & COMPLIANCE	
Certifications	RoHS compliant
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>