

## USB 2.0 All-in-One Keystone/Panel Mount Extension Cable (M/F), Angled Connector, 1 ft.

MODEL NUMBER: U024-001-KPA-BK



Adds a USB Type-A female port to a fixed location, such as a universal keystone wallplate, panel, podium or kiosk. Gives your conference room, classroom, home theater room or retail establishment a professional, clutter-free look.

### Description

The U024-001-KPA-BK USB 2.0 Hi-Speed All-in-One Keystone/Panel Mount Extension Cable allows you to terminate a USB connection in a universal keystone wallplate or panel. Or you can use the included panel mount adapter to convert the female keystone jack port for installation in a podium or kiosk. The angled connector makes the cable easy to install in tight spaces.

Ideal for giving your conference room, classroom, home theater room or retail establishment a professional, clutter-free look, this one-foot cable can complete an in-wall run and keep components out of sight in a closet or another room to eliminate cable clutter. The U024-001-KPA-BK supports data transfer rates up to 480 Mbps.

Backward compatible with earlier USB generations, the U024-001-KPA-BK features premium foil and braid shielding to deliver reliable, error-free signal quality and protection from EMI/RFI interference. Molded nickel-plated connectors with gold-plated copper contacts ensure excellent conductivity. Integral strain relief ensures the cable and connectors last a long time. A rugged PVC jacket protects twisted 28 AWG data lines and 24 AWG power lines.

### Features

#### Mount a USB 2.0 Type-A Port in a Fixed Location

- Keystone design for easy snap-in installation in wallplate or panel
- Includes panel mount adapter for installation in podium or kiosk
- Angled female connector for easy installation in tight spaces
- Data transfer rates up to 480 Mbps

### Highlights

- Connects two USB-A devices, such as computers and flash drives
- Data transfer rates up to 480 Mbps
- Premium double shielding for error-free signal quality
- Twisted 28/24 data/power lines
- Angled female connector for easy installation in tight spaces

### Package Includes

- U024-001-KPA-BK USB 2.0 Hi-Speed All-in-One Keystone/Panel Mount Extension Cable (M/F), 1 ft.



- Hides components out of sight to eliminate cable clutter
- Backward compatible with earlier USB generations

#### Premium Construction for Superior Signal Transfer

- Foil and braid shielding for error-free signal quality and EMI/RFI protection
- Molded nickel-plated connectors and gold-plated copper contacts
- Integral strain relief for long life
- Twisted 28/24 AWG data/power lines
- Rugged PVC jacket

## Specifications

OVERVIEW	
UPC Code	037332195715
INPUT	
Cable Length (ft.)	1
Cable Length (m)	0.30
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	22.86 x 1.27 x 17.78
Shipping Dimensions (hwd / in.)	9.00 x 0.50 x 7.00
Shipping Weight (kg)	0.14
Shipping Weight (lbs.)	0.30
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	DISPLAYPORT (FEMALE)
FEATURES & SPECIFICATIONS	
Technology	USB; USB 2.0 (High Speed)
STANDARDS & COMPLIANCE	
Certifications	RoHS compliant
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:  
<https://www.tripplite.com/products/product-certification-agencies>