

## USB-C Cable (M/M) - USB 2.0, 5A Rating, USB-IF Certified, Thunderbolt 3 Compatible, 2 m

MODEL NUMBER: U040-C2M-C-5A



Provides up to 20V 5A (100W) for powering and charging your MacBook Pro or other mobile device through a USB-C charger or power bank.

### Features

**USB-C to USB-C Cable Connects 2 USB-C Devices, Including MacBooks and Smartphones** This two-meter USB Type-C to Type-C cable allows you to connect one USB-C device to another. For instance, a laptop to a docking station, your smartphone to a wall charger, or a hard drive or flash drive to a computer or tablet. The USB-C to C cable is compatible with any device with a USB-C or Thunderbolt 3 port, including MacBooks, Ultrabooks and Chromebooks.

**PD Charging Cable Produces up to 100W for Rapid Syncing and Charging** The Power Delivery cable provides power output up to 5 amps (100 watts), which is sufficient for fast-charging, syncing and powering most large-capacity devices, including the MacBook Pro. It also supports USB 2.0 data transfer rates up to 480 Mbps. The USB Type-C to USB Type-C cable is backward compatible with previous USB generations, allowing you to use it with older equipment.

**Reversible USB-C Connectors Attach in Either Direction** Unlike traditional USB cables that connect in only one direction, the reversible USB-C male connectors plug into a USB-C or Thunderbolt 3 port in either direction for a fumble-free connection every time.

**USB-IF Certification Ensures Rigorous Testing and Top-of-the-Line Performance** This cable meets the high standards of USB-IF (USB Implementers Forum, Inc.), a non-profit organization consisting of companies that developed the USB specification. Receiving USB-IF certification means the U040-C2M-C-5A meets the industry's highest environmental, mechanical and electrical standards. It operates with your USB peripherals, adapters and cables with top efficiency and safety.

## Specifications

### Highlights

- Certified by USB-IF to ensure highest-grade construction and performance
- Supports USB 2.0 speeds up to 480 Mbps to ensure efficient data transfers
- Power Delivery cable provides 5A (100W) for fast-charging large-capacity devices
- Reversible USB-C plugs connect in either direction for immediate no-fuss use
- USB-C to USB-C cable is compatible with all USB-C and Thunderbolt 3 devices

### Applications

- Charge and sync a USB-C or Thunderbolt 3 mobile device from a USB-C wall charger up to 2 m away
- Transfer data between an external hard drive or flash drive and your laptop or computer
- Connect your laptop to a docking station or hub with a USB-C or Thunderbolt 3 port

### System Requirements

- Devices with USB-C or Thunderbolt 3 ports

### Package Includes

- U040-C2M-C-5A USB-C to USB-C Cable, USB-IF, M/M, 2 m



<b>OVERVIEW</b>	
UPC Code	037332241306
Technology	USB 2.0 (High Speed); USB
<b>INPUT</b>	
Cable Length (ft.)	6.6
Cable Length (m)	2
Cable Length (in.)	78.7
Cable Length (cm)	200
<b>PHYSICAL</b>	
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	4.0MM
Color	Black
Material of Construction	PVC
Unit Packaging Type	Polybag
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	14 TO 140 F (-10 TO 60 C)
Storage Temperature Range	-4 TO 185 F (-20 TO 85 C)
Relative Humidity	10% to 85%, Non-Condensing
<b>CONNECTIONS</b>	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	USB C (MALE)
Connector Plating	Nickel
Contact Plating	Gold
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Specification	USB 2.0 (up to 480 Mbps)
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	Tested to CE, FCC, RoHS, REACH, USB-IF
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>