

USB 2.0 OTG Cable with 2-in-1 Connector - Combo A Male + Micro-B Male to A Female, 6-in.

MODEL NUMBER: U052-06N-OTG-AM



Description

Tripp Lite's U052-06N-OTG-AM is a USB OTG (On-the-Go) cable that features a unique USB Micro-B / USB combo connector with a retractable USB Micro-B built into the standard USB A-Male connector. It acts as an OTG cable with the retractable Micro-B connector pulled out, connecting a USB device such as a keyboard, mouse, or flash drive to an OTG compliant Micro-B device. Push the retractable USB Micro-B connector back in to use the cable as a standard USB 2.0 A/A extension cable.

Features

- USB OTG (On-the-Go) cable featuring a unique USB Micro-B / USB combo connector with retractable Micro-B
- Acts as an OTG cable with the retractable Micro-B connector pulled out, connecting a USB device such as a keyboard, mouse, or flash drive to an OTG compliant Micro-B device
- Push the retractable USB Micro-B connector back in to use the cable as a standard USB 2.0 A/A extension cable
- USB 2.0 cable, 6-in.

Specifications

OVERVIEW	
UPC Code	037332188373
INPUT	
Cable Length (ft.)	0.5

Highlights

- USB OTG (On-the-Go) cable featuring a unique USB Micro-B / USB combo connector with retractable Micro-B
- Acts as an OTG cable with the retractable Micro-B connector pulled out, connecting a USB device such as a keyboard, mouse, or flash drive to an OTG compliant Micro-B device
- Push the retractable USB Micro-B connector back in to use the cable as a standard USB 2.0 A/A extension cable

Package Includes

- USB 2.0 OTG Cable with 2-in-1 Connector - Combo A Male + Micro-B Male to A Female, 6-in.



Cable Length (m)	0.2
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.16
Shipping Weight (lbs.)	0.35
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	MICRO-USB B (MALE)
Side B - Connector 2	USB A (FEMALE)
FEATURES & SPECIFICATIONS	
Technology	USB 2.0 (High Speed); USB
STANDARDS & COMPLIANCE	
Approvals	RoHS and REACH
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>