

## USB-C Flat Cable (M/M) - USB 2.0, Thunderbolt 3 Compatible, Black, 6 ft. (1.8 m)

MODEL NUMBER: U040-006-C-FL



Flat USB cable connects a smartphone or other USB-C device to the USB-C port on your computer, charger or power bank.

### Features

**Flat USB 2.0 Cable Charges and Syncs Your Phone or Other USB-C Mobile Device**This USB sync/charge cable (M/M) connects your smartphone, tablet, MacBook Pro, Windows laptop or other USB-C device to the USB-C port on a computer, docking station or wall charger. It supports power output up to 3 amps (60 watts), which is sufficient for fast charging and powering most mobile devices. It also simultaneously synchronizes and transfers data at USB 2.0 speeds up to 480 Mbps.

**Innovative Flat Cable Prevents Tangles, Allows Flexible Bends**Very flexible for convenient on-the-go connections, this flat cable avoids nasty tangles in your backpack or laptop bag. Its advanced flat design allows easy rolling for tangle-free storage. Plus, it bends easily for connecting to devices in tight spaces or around obstacles.

**Reversible USB-C Connectors Attach in Either Direction**Unlike traditional USB cables that connect in only one direction, the reversible USB-C male connectors plug into a USB-C or Thunderbolt 3 port in either direction for an instant connection every time.

### Highlights

- Flexible flat design helps prevent inconvenient tangling and allows easy bending
- Supports USB 2.0 speeds up to 480 Mbps to ensure efficient charging and data transfers
- Supports 3A (60W) power output for charging, syncing and powering mobile devices
- Reversible USB-C plugs connect in either direction for immediate no-fuss use
- Flat USB-C cable is compatible with all USB-C and Thunderbolt 3 devices

### Applications

- Charge and power your MacBook Pro, Windows laptop or other USB-C or Thunderbolt 3 device from a USB-C wall charger up to 6 ft. away
- Transfer data between an external hard drive and your laptop or PC
- Connect your laptop to a docking station or hub with a USB-C or Thunderbolt 3 port
- Roll tightly for convenient carrying in your laptop bag, backpack or briefcase as a flexible spare cable

### System Requirements

- Devices with USB-C or Thunderbolt 3 ports

### Package Includes



- U040-006-C-FL USB-C to USB-C Cable, M/M, Black, 6 ft. (1.8 m)

## Specifications

OVERVIEW	
UPC Code	037332254016
INPUT	
Maximum Input Amps	3
Maximum Input Watts	60
Cable Length (ft.)	6
Cable Length (m)	1.8
Cable Length (in.)	72
CHARGING	
USB Power Delivery (PD) Charging Support	Yes
PHYSICAL	
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	2.1*6.8MM
Color	Black
Material of Construction	PVC
Unit Packaging Type	Polybag
Wire Gauge (AWG)	30/22
ENVIRONMENTAL	
Operating Temperature Range	32 to 113 F (0 to 45 C)
Storage Temperature Range	-40 to 158 F (-40 to 70 C)
Operating Humidity Range	10% to 85%, Non-Condensing
Storage Humidity Range	5% to 90%, Non-Condensing
CONNECTIONS	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	USB C (MALE)



Connector Plating	Nickel
Contact Plating	Gold
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Specification	USB 2.0 (up to 480 Mbps)
Technology	USB 2.0 (High Speed); USB
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	RoHS and REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>