

## USB 2.0 All-in-One Keystone/Panel Mount Coupler Cable (F/F), Angled Connector, Black, 1 ft.

MODEL NUMBER: **U060-001-KPA-BK**



Adds a USB-A female port to a fixed location, such as a universal keystone wallplate, panel, podium or kiosk. Gives your conference room, classroom, home theater room or retail establishment a professional, clutter-free look.

### Description

The U060-001-KPA-BK USB 2.0 All-in-One Keystone/Panel Mount Coupler Cable allows you to terminate a USB Type-A connection in a universal keystone wallplate or panel. Or you can use the included panel mount adapter to convert the female keystone jack port for installation in a motherboard, podium or kiosk. The angled connector makes it easy to install in tight spaces.

Ideal for giving your conference room, classroom, home theater room or retail establishment a professional, tidy look, this one-foot cable can complete an in-wall run and keep components out of sight in a closet or another room to eliminate cable clutter.

Molded nickel-plated connectors with gold-plated contacts offer optimal signal transfer. Premium foil and braid shielding delivers reliable, error-free signal quality and protection from EMI/RFI interference. Integral strain relief ensures the cable and connectors last a long time. A rugged PVC jacket protects twisted 28 AWG data lines and 24 AWG power lines.

### Features

#### Mounts a USB 2.0 Port in a Fixed Location

- USB-A female keystone jack connector snaps easily into universal keystone wallplate or panel
- Included panel mount adapter allows installation in motherboard, podium or kiosk
- Hides components out of sight to eliminate cable clutter
- Angled female connector for easy installation in tight spaces

### Highlights

- Angled female connector for easy installation in tight spaces
- Gold-plated contacts for optimal signal transfer
- Panel mount adapter for securing to podium or kiosk
- Keystone design for snapping into standard wallplate
- Compatible with all USB-A cables

### Package Includes

- U060-001-KPA-BK USB 2.0 All-in-One Keystone/Panel Mount Coupler Cable (F/F), 1 ft.



- Compatible with all USB-A cables

#### Premium Construction for Superior Signal Transfer

- Premium foil and braid shielding for error-free signal quality and EMI/RFI protection
- Molded nickel-plated connectors with gold-plated contacts
- Integral strain relief for long life
- Twisted 28/24 AWG data/power lines
- Rugged PVC jacket

## Specifications

OVERVIEW	
UPC Code	037332195708
INPUT	
Cable Length (ft.)	1
Cable Length (m)	0.30
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.32
Shipping Weight (lbs.)	0.70
CONNECTIONS	
Side A - Connector 1	USB A (FEMALE)
Side B - Connector 1	USB A (FEMALE)
FEATURES & SPECIFICATIONS	
Technology	USB; USB 2.0 (High Speed)
CERTIFICATIONS	
Certifications	RoHS compliant
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:  
<https://www.tripplite.com/products/product-certification-agencies>