

USB to 5V DC Type-M Barrel Plug Power Cord - M/M, 28 AWG, Black, 3 ft. (0.91 m)

MODEL NUMBER: U152-003-M



USB to 5V DC power cable plugs into your 5V DC mobile device, so you can power and charge it through a computer or laptop's USB port.

Features

USB to DC Power Cable with USB-A to Type M Barrel Plug Connection You don't need to carry around a wall adapter to keep your 5V DC mobile device charged. This USB to 5V DC power cable features a male USB-A plug for connecting to a computer USB port and a male 5.5 mm (OD) x 2.1 mm (ID) Type M barrel plug for connecting to a mobile device. The U152-003-M is ideal for powering and/or charging a compatible security camera, switch, router, external hard drive, media player or other mobile device. Its three-foot length makes it convenient to carry in your backpack or laptop bag, instead of dragging around each mobile device's wall charger. Polarity: positive tip, negative sleeve.

Highlights

- USB to DC power cable is ideal for charging DC power devices from your laptop
- Great accessory for smartphones, hard drives, media players and other compatible devices
- USB-A plug connects to computer or laptop; Type M barrel plug connects to device
- More convenient charging solution than storing or carrying multiple device chargers
- 3-ft. (0.91 m) cable fits easily into backpack or laptop bag for charging on the go

Applications

- Power a security camera or other Type M network device from the USB port on a convenient laptop
- Connect an external hard drive to your laptop, eliminating the need to find a nearby outlet for the drive's bulky wall charger
- Charge a compatible smartphone or other mobile peripheral using your computer
- Plug your MP3 player or other media player into your vehicle's USB port to listen to a customized playlist

Package Includes

- U152-003-M USB to 5V DC Power Cable, 3 ft., Black

Specifications

OVERVIEW	
UPC Code	037332182616
Country/Region	Global
INPUT	
Maximum Input Amps	0
CONNECTIONS	
Side A - Connector 1	USB A (MALE)



Powering Business Worldwide

TRIPP LITE
SERIES

Side B - Connector 1	TYPE M 5V DC
PHYSICAL	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	3mm
Number of Conductors	0
Wire Gauge (OD - mm ²)	0
Cable Length (ft.)	3
Cable Length (m)	0.91
Shipping Dimensions (hwd / in.)	0.05 x 5.20 x 8.90
Shipping Dimensions (hwd / cm)	0.13 x 13.21 x 22.61
Shipping Weight (lbs.)	0.05
Shipping Weight (kg)	0.02
FEATURES & SPECIFICATIONS	
Angled Plug	No
High Voltage	No
Locking Plug	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.