

## USB 2.0 A/B Active Repeater Cable (M/M), 36 ft.

MODEL NUMBER: **U042-036**



Locate a printer or other USB peripheral 36-ft. from your computer.

### Description

Tripp Lite's High-Speed USB 2.0 Active A-B cable overcomes the 5-meter USB distance limitation with an active repeater in the middle of the cable. Now USB printers and other devices can be located up to 36-ft. away from the computer in a single, non-daisychainable run, with no need for extension cables. Full 480Mbps speed is maintained along the entire length of the cable. Backward compatible to USB 1.1. Plug-and-play, Windows and MAC compatible. The U042-036 provides up to 150mA of power to the connected device. If your device requires more than 150mA of power, it will either need to have its own power supply; or, to be plugged into a powered USB 2.0 hub (such as U222-007-R) that is connected to the U042-036.

### Features

- Connect a computer to a printer or other USB device up to 36-ft. away
- High-Speed USB 2.0 and USB 1.1 compatible
- Active repeater maintains 480Mbps signal integrity
- USB "A" to USB "B" connections
- Windows 98/ME/2000/XP/Vista/WIN7/8/10 and MAC compatible
- Cable length: 36-ft. Weight: 1 lb.
- Repeater Pod dimension: 16.75 x 57.3 x 31.7 (mm.) / 0.7 x 2.3 x 1.3 (in.)
- The U042-036 provides up to 150mA of power to the connected device. If your device requires more than 150mA of power, it will either need to have its own power supply; or, to be plugged into a powered USB 2.0 hub (such as U222-007-R) that is connected to the U042-036.

## Specifications

### Highlights

- 36-ft. USB A-B Active Cable
- Overcomes the 5-meter USB barrier
- Built-in repeater maintains high-speed USB 2.0 signal quality

### System Requirements

- A USB 2.0 port and USB 2.0 device (with type B jack) are required to meet USB 2.0 speeds. A USB 1.1 port and/or device can be used, but you will not be able to achieve USB 2.0 speeds.
- The U042-036 provides up to 150mA of power to the connected device. If your device requires more than 150mA of power, it will either need to have its own power supply; or, to be plugged into a powered USB 2.0 hub (such as U222-007-R) that is connected to the U042-036.

### Package Includes

- 36-ft. Hi-Speed USB 2.0 Active Cable



<b>OVERVIEW</b>	
UPC Code	037332138712
<b>INPUT</b>	
Cable Length (ft.)	36
Cable Length (m)	11
<b>PHYSICAL</b>	
Color	Black
Shipping Dimensions (hwd / cm)	23.11 x 26.92 x 0.25
Shipping Dimensions (hwd / in.)	9.10 x 10.60 x 0.10
Shipping Weight (kg)	0.35
Shipping Weight (lbs.)	0.77
<b>CONNECTIONS</b>	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	USB B (MALE)
<b>FEATURES &amp; SPECIFICATIONS</b>	
Technology	USB 2.0 (High Speed); USB
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>