



USB / FireWire® - 4 Port USB 1.1 Bus-Powered Hub*

MODEL NUMBER: **U203-004-R**

Description

Tripp Lite's 4-port Bus-Powered USB Hub is the ideal solution for increasing the number of available USB ports on a laptop/notebook computer. The unit features a compact design that does not require external power, software, or complicated set-up procedures. The hub features per-port overcurrent protection and plug-and-play/hot-swappable connection of devices. A 6-ft. USB AB cable is included. Tripp Lite warrants this product to be free from defects in materials and workmanship for life.

Features

- Features 4-ports to increase the number of available USB ports on a computer
- Compact design is ideal for use with a laptop/notebook computer
- Does not require external power, software, or complicated set-up procedures
- Plug-and-Play/hot-swappable allows you to add or remove a device at any time
- Fully rated for high speed transmissions (12 Mbps)
- Per-port overcurrent protection
- Diagnostic LEDs indicate power and port status
- Bus-powered - Unit receives power from connected devices
- Compatible with Windows 98, Windows 98 SE, Windows 2000, Windows ME, Windows XP and Mac OS 8.6 or higher
- 6-ft. USB AB cable included
- Tripp Lite warrants this product to be free from defects in materials and workmanship for life

Highlights

- Link multiple USB devices to 1 computer with ultra-compact hubs
- Retail packaging

System Requirements

- Computer with USB port.
- Compatible with Windows 98 or higher and Mac OS 8.5 or higher.

Package Includes

- U203-004-R 4-Port Bus-Powered USB Hub
- 6-ft. USB AB Cable

Specifications

OVERVIEW	
UPC Code	037332095725
AC Adapter	If optional power adapter is required: 5V, 2A, DC Plug: barrel type (coaxial) plug, (1.3mm/3.5mm). (Tripp Lite does not offer)
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	15.88 x 12.70 x 4.44
Shipping Dimensions (hwd / in.)	6.25 x 5.00 x 1.75
Shipping Weight (kg)	0.28
Shipping Weight (lbs.)	0.61
CONNECTIONS	
Ports	4



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Side A - Connector 1	(4) USB A (FEMALE)
Side B - Connector 1	USB A (MALE)
FEATURES & SPECIFICATIONS	
Technology	USB; USB 2.0 (High Speed)
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>