

2-in-1 OTG Adapter, USB 3.0 Micro B Male and USB 2.0 Micro B Male to USB A Female

MODEL NUMBER: U053-000-OTG



Connect a USB OTG ready Tablet or Smartphone to a USB Device

Description

This U053-000-OTG 2-in-1 USB OTG Adapter is the perfect solution for expanding the capabilities of an OTG-enabled smartPhone, tablet or other On-the-Go devices by directly connecting to USB peripherals, such as a USB thumb drive or a USB keyboard and mouse. Add a USB hub to the adapter to create additional ports to connect multiple USB devices. USB OTG technology makes this connection easy, and does not require drivers or other software...Plug-n-Play! It features multiple connectors, so you can connect to OTG-enabled devices with either a USB 2.0 Micro-B or USB 3.0 Micro-B port, and then connect the USB device directly to the USB-A port on the adapter for immediate use.

Features

- USB 3.0 Micro B Male and USB 2.0 Micro B Male to standard USB "A" Female On-The-Go (OTG) adapter
- Plug-n-Play...No Drivers or Software required
- Connect one USB device, or add a multi-port hub for multiple USB device connections

Specifications

| OVERVIEW | |
|----------------------|------------------------|
| UPC Code | 037332186904 |
| Technology | USB 2.0 (High Speed) |
| Cable Type | Passive |
| CONNECTIONS | |
| Side A - Connector 1 | USB A (FEMALE) |
| Side B - Connector 1 | MICRO-USB B (MALE) |
| Side B - Connector 2 | USB 3.0 MICRO-B (MALE) |

Highlights

- Connect Thumb Drives, Keyboards, etc to OTG Tablets and Phones
- Features both USB 3.0 Micro B and USB 2.0 Micro B connectors
- Plug-n-Play...No Software or Drivers Required

System Requirements

- USB OTG enabled Tablet, SmartPhone, or other OTG mobile device

Package Includes

- U053-000-OTG 2-in-1 OTG Adapter



Powering Business Worldwide

TRIPP LITE
SERIES

| | |
|-------------------------------------|---------------------------|
| Connector Style | Straight |
| PHYSICAL | |
| Cable Jacket Color | Black |
| Shipping Dimensions (hwd / in.) | 6.70 x 4.72 x 0.50 |
| Shipping Dimensions (hwd / cm) | 17.02 x 11.99 x 1.27 |
| Shipping Weight (lbs.) | 0.03 |
| Shipping Weight (kg) | 0.02 |
| STANDARDS & COMPLIANCE | |
| Product Compliance | RoHS |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.