

# USB 2.0 Hi-Speed or eSatA to SatA External Hard Drive Docking Station for 2.5in or 3.5in HDD

MODEL NUMBER: U239-UE1



## Description

Tripp Lite's USB 2.0 / eSATA to SATA Hard Drive Quick Dock gives you a quick and easy way to set up an external hard drive storage system. Plug the docking station into an available USB or eSATA port on your computer, and then insert a 2.5" or 3.5" SATA drive for instant access to your external storage device. Far easier than installing the hard drive internally or in a caddy, the Quick Dock is easy to use, convenient and practical. In addition, the U239-UE1 features two USB 2.0 hub ports to access your USB peripherals with. Compatible with Windows 98/ME/2000/XP/Vista/7/8, Mac OS 9.x/10.x, and Linux.

## Features

- Works with both 2.5" and 3.5" SATA hard drives
- Supports high-speed USB 2.0 data transfer rates up to 480 Mbps
- Supports SATA data transfer rates up to 3 Gbps
- Features two USB 2.0 hub ports
- Plug-n-Play (no software or configuring needed)
- Supports Windows 98/ME/2000/XP/Vista/7/8, Mac OS 9.x/10.x, Linux

## Highlights

- Works with both 2.5" and 3.5" SATA hard drives
- Supports high-speed USB 2.0 data transfer rates up to 480 Mbps
- Supports SATA data transfer rates up to 3 Gbps
- Features two USB 2.0 hub ports
- Supports Windows 98/ME/2000/XP/Vista/7/8, Mac OS 9.x/10.x, Linux

## System Requirements

- Intel compatible PC w/USB Port (USB 2.0 recommended) or eSATA port
- Windows 98/ME/2000/XP/Vista/7/8, Mac OS 9.x/10.x, Linux

## Package Includes

- U239-UE1 USB 2.0 / eSATA to SATA Hard Drive Quick Dock
- USB 2.0 Device Cable
- eSATA 7-pin Cable
- External Power Supply (100-240V, 50/60Hz, 0.8A Output: 12V,2A)
- Owner's Manual

## Specifications

OVERVIEW	
UPC Code	037332153289
Technology	SATA/eSATA; USB 2.0 (High Speed)
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	4.60 x 6.20 x 5.00



Powering Business Worldwide



Shipping Dimensions (hwd / cm)	11.68 x 15.75 x 12.70
Shipping Weight (lbs.)	1.20
Shipping Weight (kg)	0.54
Unit Dimensions (hwd / in.)	2.250 x 5.250 x 4.750
Unit Dimensions (hwd / cm)	5.7 x 13.3 x 12.1
Unit Weight (lbs.)	0.45
Unit Weight (kg)	0.20
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.