

Important Note

A new hardware version (V2) was released in 2017 that requires a different driver. Click the above Support tab to find old and new drivers and a file with instructions on how to determine which version you need.

Mini Bluetooth 4.0 (Class 1) USB Adapter

MODEL NUMBER: **U261-001-BT4**



Adds Bluetooth wireless capability via your computer or laptop's USB port. Ideal for wireless communication with Bluetooth 4.0-enabled smartphones, tablets, keyboards, mice, headsets and printers.

Description

The U261-001-BT4 Mini Bluetooth 4.0 (Class 1) USB Adapter connects to your computer or laptop's USB port to provide instant Bluetooth wireless capability. Ideal for wireless communication with Bluetooth 4.0-enabled smartphones, tablets, keyboards, mice, headsets and printers, this low-profile device protrudes less than 3/16 of an inch (5 mm) from the USB port, so it can remain connected while your laptop is inside a sleeve, briefcase or backpack.

The U261-001-BT4 has a wireless range of 164 feet (50 meters) and supports data transfer rates up to 3 Mbps. You can connect up to seven Bluetooth devices at the same time. It requires very little power to function, and its built-in security ensures your pairing, encryption and authentication remains private. It's also backward compatible with previous Bluetooth versions. Just plug the U261-001-BT4 into your Windows® or Linux computer or laptop, and the driver automatically installs.

Features

Adds Bluetooth 4.0 Wireless Capability to Your Computer or Laptop via USB

- Ideal for wireless communication with Bluetooth 4.0-enabled smartphones, tablets, keyboards, mice, headsets and printers
- Compliant with Bluetooth 4.0 LE+EDR Class 1
- Wireless range up to 164 ft. (50 m)
- Data transfer rates up to 3 Mbps
- Low power consumption

Built-In Security

- Protects your pairing, encryption and authentication info

Low-Profile Design

- Protrudes less than 3/16 in. (5 mm) from USB port

Highlights

- Compliant with Bluetooth 4.0 LE+EDR Class 1
- Wireless range up to 164 ft. (50 m)
- Connects up to 7 devices simultaneously
- Data transfer rates up to 3 Mbps
- Backward compatible with previous Bluetooth versions

System Requirements

- Available USB port
- Windows or Linux computer

Package Includes

- U261-001-BT4 Mini Bluetooth 4.0 (Class 1) USB Adapter
- Owner's manual



Powering Business Worldwide



- Remains connected while laptop is stored in briefcase or backpack

Versatile and Easy to Use

- Backward compatible with previous Bluetooth versions
- Connects easily to all Bluetooth devices
- Connects up to 7 devices simultaneously
- Plug and play—driver automatically installs upon connection

Specifications

OVERVIEW	
UPC Code	037332193452
Accessory Type	Adapter; Keyboard; Mouse
Technology	USB 2.0 (High Speed)
Accessory Class	Laptop & Tablet Accessories; USB Accessories
INPUT	
Bus Powered	Yes
POWER	
Power Consumption (Watts)	0.50
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Green (Power)
PHYSICAL	
Color	Black
Material of Construction	Steel, PVC
Shipping Dimensions (hwd / in.)	0.79 x 3.90 x 4.40
Shipping Weight (lbs.)	0.10
Unit Dimensions (hwd / in.)	0.280 x 0.870 x 0.590
Unit Packaging Type	Clamshell
Unit Weight (lbs.)	0.01
Unit Weight (kg)	0.00
ENVIRONMENTAL	
Operating Temperature Range	14° to 122°F (-10° to 50°C)

Storage Temperature Range	-4° to 158°F (-20° to 70°C)
Relative Humidity	20% to 90% RH, Non-Condensing
BTUs	1.7 BTU/Hr
COMMUNICATIONS	
Signal Range (ft.)	164
Signal Range (m)	50
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
IP68 Rated	No
IP20 Rated	No
Driver Required	Yes
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.