


Important Note

Android devices will require a USB Host Mode (OTG) cable (U052-06N) to connect the U209-005-DB25 to the device.

USB to Serial Adapter Cable (USB-A to DB25 M/M), 5 ft. (1.52 m)

MODEL NUMBER: **U209-005-DB25**



Two connection options in a single cable. Connect devices with a DB9 or DB25 serial port, such as modems, digital cameras, PDAs and ISDN terminals, to the USB Type-A port on your computer or laptop.

Features

- Connect a RS232 serial device to the USB port on your computer
- Connectors: USB-A (M); DB25 (M); DB9 (M)
- No external power is required
- Supports data transfer rates up to 230 kbps
- Premium double-shielded cable with gold-plated contacts, tinned copper braid and an aluminum Mylar foil shield that eliminates cross-talk and reduces EMI/RFI interference
- Compatible with Windows, Mac and Linux computers
- Compatible with Android tablets / phones with USB Host Mode (OTG) support and OS version 3.2 and above

Specifications

OVERVIEW	
UPC Code	037332184757
Technology	Serial; USB
Host Connector	USB A (MALE)
PHYSICAL	

Highlights

- 5 ft. cable length
- No external power is required
- Compatible with Windows, Mac and Linux computers, and Android tablets / phones (See System Requirements)
- Need drivers? Click on the Support Page link on the left

System Requirements

- Compatible with Windows 2000, XP, Server 2003, Vista, 7, Server 2008, 8, 8.1, Server 2012, 10 and 11
- Compatible with Mac OS X 10.6 through 10.12
- Compatible with Linux Redhat 7.3, 8.0 and 9.0 (Linux Kernel 2.4.31 and above; already includes built-in drivers)
- Android devices will require a USB Host Mode (OTG) cable (U052-06N) to connect the U209-005-DB25 to the device.

Package Includes

- U209-005-DB25 USB-to-Serial Adapter Cable
- DB9-to-DB25 adapter
- Owner's Manual

Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	5
Cable Length (m)	1.52
Shipping Dimensions (hwd / in.)	1.70 x 4.70 x 4.80
Shipping Dimensions (hwd / cm)	4.32 x 11.94 x 12.19
Shipping Weight (lbs.)	0.40
Shipping Weight (kg)	0.18
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	DB9 (MALE)
Side B - Connector 2	DB25 (MALE)
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty