

3-Port USB Car Charger, 36W Max - USB-C PD 3.0 Up to 18W, 2 USB-A QC 3.0 Up to 36W

MODEL NUMBER: **U280-C03-36W-1B**



3-port car charger quickly and safely charges 2 tablets, smartphones and other USB-C or USB-A devices at the same time.

Features

USB Car Charger Safely Charges 2 Mobile Devices in Your Vehicle Simultaneously This three-port USB car charger with Power Delivery (PD) 3.0 and Quick Charge (QC) 3.0 technology lets you quickly and safely charge two USB mobile devices at the same time. You and a passenger can connect your smartphones, tablets, notebooks or power banks, to name just a few compatible devices, to ensure satisfactory battery charge when you reach your destination. You can use either both USB-A ports simultaneously or one USB-A port with the USB-C port.

A Combined 36W of Charging Power Feeds Your Power-Hungry Devices When any two of them are used together, the USB-C PD 3.0 and USB-A QC 3.0 ports support up to 36W of charging power and automatically adjust to the power level most appropriate for each connected device. The fast-charging USB-C port, when used alone, provides up to 18W (5V 3A or 9V 2A) to keep your USB-C devices at capacity. The dual 18W USB-A ports adjust to a proper power level (5V 3A, 9V 2A or 12V 1.5A) to provide as much charge as your QC-compliant devices' batteries can handle.

Plugs into the 12V DC Power Outlet in Your Vehicle The compact charger connects to any standard 12V DC vehicle power outlet, such as the one on your dashboard. Just plug it in, and connect your devices' USB cables for fast, convenient mobile charging. An easy-to-see LED indicates the charger is receiving power. The U280-C03-36W-1B is compatible with Apple (including iPhone), Android (including Samsung), Windows and Amazon devices with USB-A, USB-C or Thunderbolt 3 charging ports.

Highlights

- 3-port USB charger connects to the 12V DC power outlet in your car, truck or SUV
- Ideal for charging smartphones, tablets, e-readers and notebooks while traveling
- Maximum charging power output of 36W: 18W USB-C/18W USB-A or 36W USB-A
- Prevents overheating and overcharging to shield your essential device from damage
- USB-C Power Delivery 3.0 port charges up to 4x faster than conventional USB chargers

Applications

- Charge up to 2 smartphones, tablets, power banks or e-readers while driving to your destination

System Requirements

- Vehicle with standard 12V DC power outlet

Package Includes

- U280-C03-36W-1B 3-Port USB Car Charger, Black

Specifications

OVERVIEW	
UPC Code	037332254047
Product Type	Car Charger
Charging Form Factor	Direct Plug-In
Device Compatibility	Phone; Tablet; Amazon Kindle



Over Current Protection	Yes
Technology	PD Charging; USB
INPUT	
Nominal Input Voltage(s) Supported	12V DC
Input Connection Type	12V Vehicle Lighter Port
Input Plug Type	Car Auxiliary Power Outlet
Product Length (in.)	2.22
Product Length (cm.)	5.64
Product Length (ft.)	0.19
Product Length (m.)	0.06
OUTPUT	
Output Capacity	USB-C: 18W; USB-A #1 and USB-A #2: 18W
Output (Watts)	36
Overload Protection	Yes
POWER	
USB Power Delivery (PD) Charging Support	Yes
USB Power Delivery (PD) Charging Specification	3.0
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Yellow-Green (Power)
CHARGING	
Charging Ports / Amps	(3) 3A
Number of Charging Ports	3
Total Charging Amps	4A
Charging Method	USB
Total Charging Watts	36
Charging Ports Detail	USB-C: 18W PD 3.0USB-A: 18W QC 3.0
Charging Port Type	(2) USB A (FEMALE); USB C (FEMALE)
Charging Method Detail	USB-C: Power Delivery 3.0; USB-A: QC3
PHYSICAL	
Color	Black
Material of Construction	PCB, ABS



Unit Dimensions (hwd / in.)	1.43 x 1.21 x 2.22
Unit Packaging Type	Polybag
ENVIRONMENTAL	
Operating Temperature Range	32 to 77°F (0 to 25°C)
Storage Temperature Range	-40 to 176°F (-40 to 80°C)
Operating Humidity Range	20 to 90% RH
Storage Humidity Range	5 to 90% RH
CONNECTIONS	
Ports	3
Side A - Connector 1	Car Cigarette Lighter
Side B - Connector 1	USB A (FEMALE)
Side B - Connector 2	USB A (FEMALE)
Side B - Connector 3	USB C (FEMALE)
FEATURES & SPECIFICATIONS	
Driver Required	No
Quick Charge Compliant	3.0
SPECIAL FEATURES	
Overcurrent Protection	Yes
Overvoltage Protection	Yes
GaN Technology	No
STANDARDS & COMPLIANCE	
Certifications	CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>