

10W Wireless Fast-Charging Stand with International AC Adapter, Black

MODEL NUMBER: U280-Q01ST-P-BK



10-watt wireless phone charger transfers battery power to your Qi-enabled device without connecting a cable between them.

Features

Wireless Cell Phone Charger Delivers up to 10W for Apple and Samsung Phones

Who wants to plug and unplug cords when you just want to charge your cell phone? The U280-Q01ST-P-BK makes charging more convenient by doing it wirelessly. Just place your Qi-certified device, such as an iPhone, Pixel or Galaxy smartphone, on the charging stand. That's all there is to it. This wireless phone charger even works through most protective phone cases up to 5 millimeters. Note: Please remove any magnetic or metal objects from your phone or case before charging.

Compatible with Qi-Certified Cell Phones to Ensure a Safe, Flawless Charge

The U280-Q01ST-P-BK charges all Qi smartphones from Apple, Sony, LG, Samsung, Nokia and other popular brands in either portrait or landscape orientation. It protects your expensive device from overheating and overcharging that could lead to internal damage. An LED glows blue to indicate the charging process is underway and flashes blue to indicate any charging error.

Compact Stand Fits Comfortably on Any Counter, Table or Workspace

The portable lightweight stand is just four inches in height, so it takes up hardly any space on your desktop or bedside table. An included international power supply connects the charger to a convenient AC outlet.

Specifications

OVERVIEW	
UPC Code	037332259622
Product Type	Wireless Charger
Charging Form Factor	Pad/Stand
Device Compatibility	Phone

Highlights

- Charges your smartphone through its protective case to avoid the hassle of removing it
- LED glows blue during charging and flashes blue to indicate a charging error
- Prevents overheating and overcharging to protect your essential device from damage
- Lightweight portable design takes up little space on your desk or bedside table
- Universally compatible with all Qi-certified smartphones and other devices

Applications

Transfer power from the included power adapter to your smartphone's battery without the burden of carrying and connecting extra cabling

System Requirements

Compatible with all Qi-certified smartphones, including the latest Apple iPhone, Google Pixel and Samsung Galaxy devices

Package Includes

- U280-Q01ST-P-BK Wireless Fast-Charging Stand, Black
- International Power Supply (12V 2A)
- Quick Start Guide

Technology	USB; Wireless
INPUT	
Nominal Input Voltage(s) Supported	12V DC
Input Plug Type	DC Plug (Barrel type)
OUTPUT	
Output Capacity (Watts)	10
Overload Protection	Yes
POWER	
Power Source Type	AC Adapter
External Power Supply Plug(s)	AS/NZS 3112 Australia; BS 1363 UK; CEE 7/16 Schuko; NEMA 1-15P North America
External Power Supply Output Specs (V / A)	12V / 2A
Power Consumption (Watts)	10
USB Power Delivery (PD) Charging Support	No
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Blue - Connection
CHARGING	
Number of Charging Ports	0
Total Charging Amps	0.7A
Total Charging Watts	10
Charging Method	Wireless
Charging Port Type	WIRELESS CHARGING COIL
Charging Ports Details	5V/1A (5W); 9V/1.1A (10W)
PHYSICAL	
Color	Black
Material of Construction	PC (Plastic)
Unit Dimensions (hwd / in.)	0.380 x 4.120 x 4.120
Unit Dimensions (hwd / cm)	9.7 x 10.2 x 10.2
Unit Packaging Type	Box
Unit Weight (lbs.)	0.172
Unit Weight (kg)	0.08

ENVIRONMENTAL	
Operating Temperature Range	32 to 95 °F (0 to 35 °C)
Storage Temperature Range	-4 to 158 °F (-20 to 70 °C)
Operating Humidity Range	10% to 80% RH
Storage Humidity Range	5% to 95% RH
CONNECTIONS	
Side A - Connector 1	USB C (FEMALE)
Side B - Connector 1	WIRELESS CHARGING COIL
FEATURES & SPECIFICATIONS	
Driver Required	No
Quick Charge Compliant	No
Overcurrent Protection	Yes
Overvoltage Protection	Yes
GaN Technology	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty