

USB 3.0 All-in-One Keystone/Panel Mount Extension Cable (M/F), Angled Connector, Black, 1 ft. (0.31 m)

MODEL NUMBER: U324-001-KPA-BK



Adds a USB 3.0 female port to a fixed location, such as a universal keystone wallplate, panel, podium or kiosk. Gives your conference room, classroom, home theater room or retail establishment a professional, clutter-free look.

Features

Mounts a USB 3.0 Port in a Fixed Location

- USB-A female keystone jack connector snaps easily into universal keystone wallplate or panel
- Included panel mount adapter allows installation in motherboard, podium or kiosk
- Supports USB 3.0 data transfer rates up to 5 Gbps
- Hides components out of sight to eliminate cable clutter
- Angled female connector for easy installation in tight spaces
- Compatible with all USB-A cables

Premium Construction for Superior Signal Transfer

- Premium foil and braid shielding for error-free signal quality and EMI/RFI protection
- Molded nickel-plated connectors with gold-plated contacts
- Integral strain relief for long life
- Twisted 28/24 AWG data/power lines
- Rugged PVC jacket

Specifications

OVERVIEW

Highlights

- Connects two USB-A devices, such as computers and flash drives
- Supports USB 3.0 data transfer rates up to 5 Gbps
- Twisted 28/24 data/power lines
- Gold-plated contacts for optimal signal transfer
- Angled female connector for easy installation in tight spaces

Package Includes

- U324-001-KPA-BK USB 3.0 All-in-One Keystone/Panel Mount Extension Cable (M/F), 1 ft.



UPC Code	037332195661
Technology	USB; USB 3.0 (SuperSpeed); USB 3.1 (Gen 1)
INPUT	
Cable Length (ft.)	1
Cable Length (m)	0.30
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	0.64 x 17.53 x 24.76
Shipping Dimensions (hwd / in.)	0.25 x 6.90 x 9.75
Shipping Weight (kg)	0.04
Shipping Weight (lbs.)	0.09
CONNECTIONS	
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	USB 3.0 A (FEMALE)
STANDARDS & COMPLIANCE	
Certifications	RoHS compliant
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>