

USB 3.0 SuperSpeed Extension Cable - USB M/F, Black, 3 ft. (0.91 m)

MODEL NUMBER: U324-003-BK



3 ft. extension cord connects two devices with USB-A connectors or extends your existing USB cable by 3 feet.

Features

3-ft. (0.91 m) Extension Cable Connects Computers, Printers, Modems and Other USB Equipment

This USB 3.0 SuperSpeed Type-A Extension Cable (M/F) attaches to your current USB 3.0 cable to extend it by three feet. It connects your computer, laptop or other compatible USB 3.0 device, such as a Chromebook or Surface tablet, to a USB-A keyboard, printer, portable hard drive, patch panel or other peripheral. The three-foot length helps reduce cable clutter and minimize the risk of tripping.

Transfers Data at SuperSpeed Transfer Rates up to 5 Gbps The U324-003-BK supports USB 3.0 speeds up to 5 Gbps—ten times the speed of USB 2.0—and better power efficiency with no device polling and lower active and idle power requirements. The cable's bi-directional data interface allows data to flow both directions simultaneously, increasing theoretical bandwidth by 10 times. The cable is backward compatible with previous USB generations, allowing you to use it with legacy devices.

Highlights

- Recommended for connecting computers, hard drives and other USB-A devices
- Supports USB 3.0 SuperSpeed data transfer rates up to 5 Gbps—10x faster than USB 2.0
- Bi-directional data interface allows data to flow both directions simultaneously
- Adds 3-ft. (0.91 m) to your existing USB connection to provide flexibility in placing devices
- Ideal replacement for worn-out or missing 3-ft. (0.91 m) extension cord

Applications

- Connect devices like computers, servers and external hard drives in your data center, workspace or home theater
- Extend an existing USB connection up to 3-ft. (0.91 m) to more easily place a device
- Provide a high-quality replacement for a worn-out or missing power cord

System Requirements

- Devices and cable with USB-A connectors (USB 3.0 capability required to reach USB 3.0 speeds)

Package Includes

- U324-003-BK USB 3.0 SuperSpeed Extension Cable, A to A, M/F, Black, 3-ft. (0.91 m)

Specifications

OVERVIEW	
UPC Code	037332224859
Technology	USB 3.x
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	USB A (FEMALE)



Powering Business Worldwide

TRIPP LITE
SERIES

Connector Plating	Nickel
Connector Style	Straight
PHYSICAL	
Material of Construction	PVC
Cable Jacket Color	Black
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	5.5
Cable Length (ft.)	3
Cable Length (m)	0.91
Cable Length (in.)	36
Unit Packaging Type	Polybag
ENVIRONMENTAL	
Operating Temperature Range	32° to 122°F (0° to 50°C)
Storage Temperature Range	-13° to 185°F (-25° to 85°C)
Relative Humidity	15 ~ 85% Relative Humidity
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.0 (up to 5 Gbps)
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.