

A new hardware version (V2) was released in 2017 that requires a different driver. Click the above Support tab to find old and new drivers and a file with instructions on how to determine which version you need.

Mini Bluetooth 4.0 (Class 1) USB Adapter

MODEL NUMBER: **U261-001-BT4**



Adds Bluetooth wireless capability via your computer or laptop's USB port. Ideal for wireless communication with Bluetooth 4.0-enabled smartphones, tablets, keyboards, mice, headsets and printers.

Description

The U261-001-BT4 Mini Bluetooth 4.0 (Class 1) USB Adapter connects to your computer or laptop's USB port to provide instant Bluetooth wireless capability. Ideal for wireless communication with Bluetooth 4.0-enabled smartphones, tablets, keyboards, mice, headsets and printers, this low-profile device protrudes less than 3/16 of an inch (5 mm) from the USB port, so it can remain connected while your laptop is inside a sleeve, briefcase or backpack.

The U261-001-BT4 has a wireless range of 164 feet (50 meters) and supports data transfer rates up to 3 Mbps. You can connect up to seven Bluetooth devices at the same time. It requires very little power to function, and its built-in security ensures your pairing, encryption and authentication remains private. It's also backward compatible with previous Bluetooth versions. Just plug the U261-001-BT4 into your Windows® or Linux computer or laptop, and the driver automatically installs.

Features

Adds Bluetooth 4.0 Wireless Capability to Your Computer or Laptop via USB

- Ideal for wireless communication with Bluetooth 4.0-enabled smartphones, tablets, keyboards, mice, headsets and printers
- Compliant with Bluetooth 4.0 LE+EDR Class 1
- Wireless range up to 164 ft. (50 m)
- Data transfer rates up to 3 Mbps
- Low power consumption

Highlights

- Compliant with Bluetooth 4.0 LE+EDR Class 1
- Wireless range up to 164 ft. (50 m)
- Connects up to 7 devices simultaneously
- Data transfer rates up to 3 Mbps
- Backward compatible with previous Bluetooth versions

System Requirements

- Available USB port
- Windows or Linux computer

Package Includes

- U261-001-BT4 Mini Bluetooth 4.0 (Class 1) USB Adapter
- Owner's manual



Built-In Security

- Protects your pairing, encryption and authentication info

Low-Profile Design

- Protrudes less than 3/16 in. (5 mm) from USB port
- Remains connected while laptop is stored in briefcase or backpack

Versatile and Easy to Use

- Backward compatible with previous Bluetooth versions
- Connects easily to all Bluetooth devices
- Connects up to 7 devices simultaneously
- Plug and play—driver automatically installs upon connection

Specifications

OVERVIEW	
UPC Code	037332193452
INPUT	
Bus Powered	Yes
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Green (Power)
PHYSICAL	
Unit Packaging Type	Clamshell
Unit Dimensions (hwd / in.)	0.28 x 0.87 x 0.59
Unit Weight (lbs.)	0.01
Unit Weight (kg)	0.00
Material of Construction	Steel, PVC
Color	Black
ENVIRONMENTAL	
Operating Temperature Range	14 to 122 F (-10 to 50 C)
Storage Temperature Range	-4 to 158 F (-20 to 70 C)
Relative Humidity	20% to 90% RH, Non-Condensing
BTUs	1.7 BTU/Hr
Power Consumption (Watts)	0.5



COMMUNICATIONS	
Signal Range (ft.)	164
Signal Range (m)	50
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
Driver Required	Yes
Technology	USB 2.0 (High Speed); USB
CERTIFICATIONS	
Certifications	Tested to CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>