

## Dual-Port USB Tablet / Phone Car Charger, 5V 3.1A / 15.5W

MODEL NUMBER: U280-002-C12



### Highlights

- Quickly charges two devices at one time
- 5V / 2.1A USB port for tablets; 5V / 1.0A USB port for phone

### System Requirements

- Automobile 12V DC Lighter Socket

### Package Includes

- Dual USB Tablet Phone Car Charger, 3.1A

Charge your Tablet and Phones simultaneously in your car

### Description

The 3.1A Dual USB Car Charger allows you to quickly and safely charge two USB-powered devices simultaneously. Its dual-port interface features one 5V 2.1A USB charging port, ideal for ultra-fast charging of devices, and one 5V 1A USB charging port for iPhone, iPod and other USB-powered devices. This high-quality and ultra-compact charger works with any standard in-vehicle power outlet and features a translucent ring around the USB ports that glows blue to indicate power being passed through. It is a handy tool to keep your devices fully charged and ready to use while you are on the go.

### Features

- High Speed Dual 2.1A USB ports for charging multiple devices, including tablets, eReaders, Smartphone's and more.
- Works with any 12V DC Auto lighter socket
- Use your existing USB cables to charge all devices
- Dual USB ports: 1 x 2.1A, 1 x 1.0A

## Specifications

OVERVIEW	
UPC Code	037332184283
Product Type	Car Charger
Charging Form Factor	Direct Plug-In
Device Compatibility	Phone; Tablet; Amazon Kindle
INPUT	
Nominal Input Voltage(s) Supported	12V DC
Input Plug Type	Car Auxiliary Power Outlet



Powering Business Worldwide

TRIPP LITE  
SERIES

OUTPUT	
Overload Protection	Yes
CONNECTIONS	
Number of Ports	2
Side A - Connector 1	Car Cigarette Lighter
Side B - Connector 1	(2) USB A (FEMALE)
CHARGING	
Number of Charging Ports	2
Total Charging Amps	3.1A
Total Charging Watts	15.5
Charging Method	USB
Charging Port Type	(2) USB A (FEMALE)
Charging Ports Details	USB-A: 5V 2.1A (10.5W)USB-A: 5V 1A (5W)
Charging Ports / Amps	(1) 1A; (1) 2.1A
PHYSICAL	
Color	White
Shipping Dimensions (hwd / in.)	5.90 x 3.90 x 0.50
Shipping Dimensions (hwd / cm)	14.99 x 9.91 x 1.27
Shipping Weight (lbs.)	0.04
Shipping Weight (kg)	0.02
FEATURES & SPECIFICATIONS	
GaN Technology	No
Overcurrent Protection	Yes
Overvoltage Protection	Yes
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty



*Powering Business Worldwide*

TRIPP LITE  
SERIES

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.