

## USB 3.0 SuperSpeed to HDMI Dual Monitor External Video Graphics Card Adapter, 512 MB SDRAM - 2048x1152,1080p

MODEL NUMBER: U344-001-HDMI-R



### Description

Tripp Lite's U344-001-HDMI-R USB 3.0 to HDMI Multi Monitor External Video Adapter allows you to connect an additional monitor or projector to the USB 3.0 port on your computer/laptop. Up to six adapters can be used simultaneously, allowing the user to connect up to six additional monitors to a single computer. Once the installation is done, the computer screen appears on the add-on monitor(s) without the hassle of function keys to swap to a second monitor. Supports video resolutions up to 2048 x 1152 (60Hz), 1080p (60Hz). Windows and Intel Mac compatible.

### Features

- Add an additional HDMI monitor/TV through a single USB 3.0 port
- Use up to six adapters simultaneously, adding up to six additional monitors/TVs to a single computer
- View large spreadsheets across multiple screens by extending video amongst all monitors
- Play video on one monitor while working on another
- Do multiple screen presentations from a laptop computer
- Bus powered...no external power adapter needed
- Features 512MB DDR2 SDRAM of memory
- Supports video resolutions up to 2048 x 1152 (60Hz), 1080p (60Hz)
- Compatible with Windows 7 and later. Supports both 32- and 64-bit.
- Supports Surface tablets running non-RT Windows 8, 8.1 and 10
- Compatible with Intel Mac OS X 10.8.5 and later, Supports Mac 10.11. Supports both 32- and 64-bit.
- Uses DisplayLink DL3500 chipset

## Specifications

### Highlights

- Connect a HDMI TV to a computer's USB 3.0 port
- Up to six adapters can be added to one computer
- Features 512MB DDR2 SDRAM of memory
- Supports video resolutions up to 2048 x 1152 (60Hz), 1080p (60Hz)
- Windows and Intel Mac compatible
- Compatible with Ubuntu 14.04.2

### System Requirements

- Compatible with Windows 7 and later. Supports both 32- and 64-bit.
- Supports Surface tablets running non-RT Windows 8, 8.1 and 10
- Compatible with Intel Mac OS X 10.8.5 and later, Mac 10.11. Supports both 32- and 64-bit.
- Reference the owner's manual for system requirements when using multiple adapters or when using the add-on monitor for DVD playback.

### Package Includes

- (1) U344-001-HDMI-R
- (1) Driver CD
- (1) USB 3.0 Cable
- (1) Owner's Manual



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

| <b>OVERVIEW</b>                      |                                 |
|--------------------------------------|---------------------------------|
| UPC Code                             | 037332174208                    |
| <b>PHYSICAL</b>                      |                                 |
| Color                                | Black                           |
| Shipping Dimensions (hwd / cm)       | 2.29 x 13.46 x 8.89             |
| Shipping Dimensions (hwd / in.)      | 0.90 x 5.30 x 3.50              |
| Shipping Weight (kg)                 | 0.09                            |
| Shipping Weight (lbs.)               | 0.19                            |
| <b>CONNECTIONS</b>                   |                                 |
| Side A - Connector 1                 | USB 3.0 A (MALE)                |
| Side B - Connector 1                 | HDMI (FEMALE)                   |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                                 |
| Technology                           | USB 3.0 (SuperSpeed); HDMI; USB |
| <b>WARRANTY</b>                      |                                 |
| Product Warranty Period (Worldwide)  | 3-year limited warranty         |

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>