

Dual Wireless Charging Pad, Qi-Certified, Black

MODEL NUMBER: U280-Q02FL-BK



10W wireless charging pad transfers battery power to 2 devices at the same time without connecting cumbersome cables to them.

Features

Wireless Cell Phone Charger Delivers up to 10W for Apple and Samsung Devices

Who wants to plug and unplug power cords when you just want to charge your phones? The U280-Q02FL-BK makes charging more convenient by doing it wirelessly. Just place your Qi-certified devices on the charging pad. That's all there is to it. This wireless phone charger even works through most protective phone cases up to 5 millimeters. It charges one smartphone at 10 watts or two phones simultaneously at 5 watts each. An included power supply connects the charger to a wall outlet, surge protector or PDU.

Note: please remove any magnetic or metal objects from your phone or case before charging.

Compatible with Qi-Certified Mobile Devices to Ensure a Safe, Flawless Charge

The U280-Q02FL-BK works with all Qi smartphones, tablets and other devices from Apple, Sony, LG, Samsung, Nokia and other popular brands. It protects your expensive devices from overheating and overcharging that could lead to internal damage. Two-color LEDs monitor charging and inform you of charge status, error or over-temperature. The portable lightweight pad fits easily on your desktop or bedside table.

Highlights

- Charges 2 Apple, Google, Samsung and other Qi smartphones simultaneously at 5W each
- Intelligent 2-color LEDs indicate charging status, error or over-temperature warning
- Prevents overheating and overcharging to protect your essential devices from damage
- Charges your smartphone through its protective case to avoid the hassle of removing it
- Universally compatible with all Qi-certified smartphones and other devices

Applications

Transfer power from an AC outlet to your smartphones' batteries without the burden of carrying and connecting extra cabling

System Requirements

Compatible with all Qi-certified smartphones, tablets and other devices from popular brands including Apple, Samsung, Google, LG, Sony, Nokia, Microsoft, Motorola, ZTE and Xiaomi

Package Includes

- U280-Q02FL-BK Dual Wireless Charging Pad, Black
- External power supply with 5 ft. cord (Input: 100–240V, 50/60 Hz, 0.8A; Output: 12V 2.5A)
- (4) International plug adapters (North America, U.K., Europe, Australia)
- Quick Start Guide



Specifications

OVERVIEW	
UPC Code	037332257260
Device Compatibility	Phone; Tablet
Over Current Protection	Yes
Technology	USB; Wireless
INPUT	
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
External Power Supply Plug(s)	AS/NZS 3112 Australia; BS 1363 UK; CEE 7/16 Schuko; NEMA 1-15P North America
OUTPUT	
Output Capacity	5V/1A (5W); 9V/1.1A (10W)
Output (Watts)	10
POWER	
External Power Supply Input Specs (V / Hz / A)	100-240V ~ 50/60Hz, 0.8A
External Power Supply Output Specs (V / A)	12V, 2.5A
External Power Supply Cord Length (ft.)	4.9
External Power Supply DC Barrel Connector Specs	OD: 3.5 x 1.35 x 9.5mm, Positive Pin, Negative Sleeve
External Power Supply Certifications	CE; UL; cUL
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Blue (Power, Charging, Standby); Green (FOD, Over-Temperature Protection, Wrong Charger)
CHARGING	
Number of Charging Ports	0
Charging Method	Wireless
PHYSICAL	
Color	Black
Material of Construction	PC + ABS
Unit Dimensions (hwd / cm)	19.5 x 1.23 x 9.0
Unit Dimensions (hwd / in.)	7.677 x 0.484 x 3.543
Unit Packaging Type	Box



Unit Weight (kg)	0.15
Unit Weight (lbs.)	0.330
ENVIRONMENTAL	
Operating Temperature Range	32 to 95 °F (0 to 35 °C)
Storage Temperature Range	-4 to 158 °F (-20 to 70 °C)
Operating Humidity Range	10 to 80% RH
Storage Humidity Range	5 to 95% RH
CONNECTIONS	
Side A - Connector 1	3.5mm x 1.35mm (5V DC Barrel)
Side B - Connector 1	(2) WIRELESS CHARGING COIL
FEATURES & SPECIFICATIONS	
Driver Required	No
STANDARDS & COMPLIANCE	
Certifications	CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>