

USB 3.0 SuperSpeed Extension Cable - USB-A to USB-A, M/F, Black, 3 ft. (0.9 m)

MODEL NUMBER: U324-003-BK



3-foot extension cord connects two devices with USB-A connectors or extends your existing USB cable by 3 feet.

Features

3-Foot Extension Cable Connects Computers, Printers, Modems and Other USB Equipment This USB 3.0 SuperSpeed Type-A Extension Cable (M/F) attaches to your current USB 3.0 cable to extend it by three feet. It connects your computer, laptop or other compatible USB 3.0 device, such as a Chromebook or Surface tablet, to a USB-A keyboard, printer, portable hard drive, patch panel or other peripheral. The three-foot length helps reduce cable clutter and minimize the risk of tripping.

Transfers Data at SuperSpeed Transfer Rates up to 5 Gbps The U324-003-BK supports USB 3.0 speeds up to 5 Gbps—ten times the speed of USB 2.0—and better power efficiency with no device polling and lower active and idle power requirements. The cable's bi-directional data interface allows data to flow both directions simultaneously, increasing theoretical bandwidth by 10 times. The cable is backward compatible with previous USB generations, allowing you to use it with legacy devices.

Highlights

- Recommended for connecting computers, hard drives and other USB-A devices
- Supports USB 3.0 SuperSpeed data transfer rates up to 5 Gbps—10x faster than USB 2.0
- Bi-directional data interface allows data to flow both directions simultaneously
- Adds 3 ft. to your existing USB connection to provide flexibility in placing devices
- Ideal replacement for worn-out or missing 3 ft. extension cord

Applications

- Connect devices like computers, servers and external hard drives in your data center, workspace or home theater
- Extend an existing USB connection up to 3 ft. to more easily place a device
- Provide a high-quality replacement for a worn-out or missing power cord

System Requirements

- Devices and cable with USB-A connectors (USB 3.0 capability required to reach USB 3.0 speeds)

Package Includes

- U324-003-BK USB 3.0 SuperSpeed Extension Cable, A to A, M/F, Black, 3 ft.



Specifications

OVERVIEW	
UPC Code	037332224859
INPUT	
Cable Length (ft.)	3
Cable Length (m)	1
Cable Length (in.)	36
PHYSICAL	
Wire Gauge (AWG)	28/24
Unit Packaging Type	Polybag
Material of Construction	PVC
Color	Black
Cable Outer Diameter (OD)	5.5
Cable Jacket Rating	VW-1
ENVIRONMENTAL	
Operating Temperature Range	32 ~ 122F (0 ~ 50C)
Storage Temperature Range	-13 ~ 185F (-25 ~ 85C)
Relative Humidity	15 ~ 85% Relative Humidity
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	USB A (FEMALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.0 (up to 5 Gbps)
Technology	USB 3.0 (SuperSpeed)
CERTIFICATIONS	
Certifications	Tested to RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>