

2-Port USB 3.x (5Gbps) Peripheral Sharing Switch

MODEL NUMBER: U359-002



Connects a single USB printer or other peripheral to 2 computers simultaneously to save time, money and precious workspace.

Features

USB Sharing Switch Connects 2 Computers to One USB Printer, Scanner or Other Device This compact 2-port USB peripheral-sharing switch lets you share one USB 3.0 peripheral between two computers in your home or small office. This eliminates the cost and effort of picking out and buying two printers, two scanners, two external hard drives, etc., as well as the problem of where to put them and their cables. By sharing a USB 3.0 printer or webcam between two computers, you save time, money and precious workspace. Maximum distance from host device to peripheral is 16-ft. (4.88 m).

Supports SuperSpeed USB 3.0 to Ensure Fast Data Transfers This USB 3.0 sharing switch supports USB 3.0 data transfer rates up to 5 Gbps, which is 10 times faster than USB 2.0. It is especially recommended for high-bandwidth USB 3.0 devices, such as security cameras and high-resolution webcams. The USB 3.0 peripheral-sharing switch is backward compatible with previous USB generations, so you can continue using older peripherals while getting maximum performance from current devices.

Switch Between Computers with a Quick Touch of a Button Easy one-touch port switching lets you switch from one computer to the other just by pressing the buttons on top of the unit. Blue LEDs indicate which computer is currently in control of the connected USB 3.0 peripheral.

Ready to Use Right from the Package, So You Can Plug and Play Immediately The USB sharing switch requires no external power supply or software and drivers to download and install. Just connect your USB 3.0 peripheral device to the switch's USB-A port and the computers to the switch's USB-B ports with user-supplied USB 3.0 cables. The USB 3.0 sharing switch supports all USB-enabled operating systems.

Specifications

OVERVIEW	
UPC Code	037332224774
Technology	USB 3.x

Highlights

- Share a printer, scanner, hard drive, webcam or other USB device with 2 computers
- Supports SuperSpeed USB 3.0 speeds up to 5 Gbps to ensure fast data transfers
- Easy one-touch control lets you switch between computers using manual buttons
- Backward compatible with USB 2.0 and 1.1 devices, so you can use older peripherals
- Plug-and-play operation with no software required for easy, immediate installation

Applications

- Switch one printer or scanner between 2 computers to save space in the office
- Connect an external hard drive, so both computers can access the same data
- Control 2 computers using the same USB keyboard/mouse combo
- Connect a webcam or security camera to monitor inventory or an office lobby from multiple computers

System Requirements

- Up to 2 computers with USB-A ports
- Peripheral with USB-A port

Package Includes

- U359-002 2-Port USB 3.0 Peripheral Sharing Switch - SuperSpeed
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

Host Connector	USB A (MALE)
VIDEO	
Extended Mode	No
Mirror Mode	No
DisplayPort Alt Mode	No
DATA	
Data Ports	USB A (FEMALE)
INPUT	
Bus Powered	Yes
CONNECTIONS	
Number of Ports	3
Side A - Connector 1	USB 3.0 A (FEMALE)
Side B - Connector 1	(2) USB 3.0 B (FEMALE)
Connector Plating	Nickel
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Blue (Display Control)
PHYSICAL	
Color	Black
Material of Construction	ABS
Shipping Dimensions (hwd / in.)	1.46 x 3.07 x 2.48
Shipping Dimensions (hwd / cm)	3.71 x 7.80 x 6.30
Shipping Weight (lbs.)	0.14
Shipping Weight (kg)	0.06
Unit Dimensions (hwd / in.)	2.800 x 2.200 x 0.800
Unit Dimensions (hwd / cm)	7.1 x 5.6 x 2
Unit Packaging Type	Box
Unit Weight (lbs.)	0.01
Unit Weight (kg)	0.00
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	14° to 131°F (-10° to 55°C)
Operating Humidity Range	5% to 90% RH, Non-Condensing



Powering Business Worldwide

TRIPP LITE
SERIES

Storage Humidity Range	5% to 95% RH, Non-Condensing
FEATURES & SPECIFICATIONS	
USB Hub Ports	Yes
Number of USB Hub Ports	1
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps); USB 3.2 Gen 1 (up to 5 Gbps)
Port Selection	Pushbutton
Driver Required	No
STANDARDS & COMPLIANCE	
TAA Compliant Option	N
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA); UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.