

Use only the external power supply that comes with your hub. Beginning in the fall of 2015, a 12V 2A power supply will be included with the U360-007, whereas previous units included a 5V 4A power supply. The power spec printed under the DC jack on your hub will match the spec of the included power supply.

7-Port USB 3.0 SuperSpeed Hub with USB Charging

MODEL NUMBER: **U360-007**



Connects to the USB 3.0 port on your laptop, Ultrabook or computer to give you seven external USB 3.0 ports.

Description

Tripp Lite's U360-007 USB 3.0 Hub plugs into a computer's USB 3.0 port and provides seven USB 3.0 SuperSpeed peripheral ports, as well as USB charging. Plug-and-Play... no software or drivers required. Automatically switches to the highest speed supported by the peripheral. Windows (compatible with Windows 10) and Mac compatible.

Features

- 7-Port USB 3.0 SuperSpeed Hub with USB Charging
- Supports USB 3.0 5Gbps transfer speeds when plugged into a USB 3.0 computer and peripheral
- Each USB-A port is capable of delivering up to 5V, 2.4A and is USB Battery Charging (BC) specification v1.2 compliant
- The included external power supply provides 12V 2A of power, to be shared between the hubs ports
- Plug-and-Play
- No software or drivers required
- Windows (compatible with Windows 10) and Mac compatible
- Overcurrent protection
- LED power indicator light

Highlights

- USB 3.0 Hub with 7 USB 3.0 SuperSpeed ports and USB Charging
- Plug-and-Play - no software or drivers required
- All 7 USB-A ports provide up to 5V, 2.4A of charging power each and are USB Battery Charging (BC) specification v1.2 compliant.

System Requirements

- Computer with an available USB 3.0 port
- USB peripherals (backward compatible with previous USB generations)
- Use only the external power supply that comes with your hub. Beginning in the fall of 2015, a 12V 2A power supply will be included with the U360-007, whereas previous units included a 5V 4A power supply. The power spec printed under the DC jack on your hub will match the spec of the included power supply.

Package Includes

- USB 3.0 7-port Hub with USB Charging
- USB 3.0 A-B cable, 3ft
- External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.8A Max / Output: 12V, 2A)



Specifications

OVERVIEW	
UPC Code	037332178480
AC Adapter	Input: 100-240V, 50/60Hz, 0.8A Max / Output: 12V, 2A
Over Current Protection	2.93A
OUTPUT	
Charging Ports / Amps	(1) 2A
INPUT	
Voltage Compatibility (VAC)	100; 110; 120; 127; 200; 208; 220; 230; 240
External Power Supply Input Specs (V / Hz / A)	100-240V / 50/60Hz / 1.5A
External Power Supply Output Specs (V / A)	12V / 3A
External Power Supply Cord Length (ft.)	5
External Power Supply DC Barrel Connector Specs	OD: 5.5 x 2.5 x 10mm, Positive Pin, Negative Sleeve
External Power Supply Plug(s)	NEMA 1-15P North America
External Power Supply Certifications	cUL; RoHS
Bus Powered	No
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Blue (Power)
PHYSICAL	
Shipping Dimensions (hwd / in.)	5.51 x 5.91 x 3.54
Shipping Dimensions (hwd / cm)	14.00 x 15.01 x 8.99
Shipping Weight (lbs.)	0.79
Shipping Weight (kg)	0.36
Unit Packaging Type	Box
Unit Dimensions (hwd / in.)	0.87 x 6.1 x 2
Unit Weight (lbs.)	0.00
Unit Weight (kg)	0.00
Material of Construction	ABS
Color	Black



ENVIRONMENTAL	
Operating Temperature Range	-4 to 158 F (-20 to 70 C)
Storage Temperature Range	-4 to 185 F (-20 to 85 C)
Relative Humidity	20% to 80% RH, Non-Condensing
BTUs	4.8 BTU/Hr
Power Consumption (Watts)	1.4
Power Provided to Connected Device(s)	5V 0.9A (4.5W) Output (USB-A 3.0), 5V 2A (10W) Output (USB 2A Charger)
CONNECTIONS	
Ports	7
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	(7) USB 3.0 A (FEMALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
Technology	USB; USB 3.0 (SuperSpeed)
CERTIFICATIONS	
Certifications	Tested to CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>