

## USB-C to USB-A Cable (M/M), USB 3.1 Gen 2 (10 Gbps), Thunderbolt 3 Compatible, 20-in. (50.8 cm)

MODEL NUMBER: U428-20N-G2



USB-C 3.1 to USB-A cable connects a smartphone or other USB-C device to the USB-A port on your computer, wall charger or car charger.

### Features

**USB Type-C to USB Type-A Cable Connects a USB-C Mobile Device to a Wall Charger** This 20-inch USB-C 3.1 to USB-A cable allows you to connect any device with a USB-C or Thunderbolt 3 port, including MacBooks, Ultrabooks and Chromebooks, to a USB-enabled computer, charger, hard drive or other peripheral for the purpose of charging, powering, syncing or transferring data. Its 20-inch length makes it easy to carry in your briefcase or laptop bag for quick downloads and file transfers on the go.

**Charges Devices and Transfers Data at Lightning-Fast USB 3.1 Gen 2 Speeds** The USB-C to USB-A cable supports USB 3.1 Gen 2 data transfer rates up to 10 Gbps, which is double the speed of Gen 1. The Power Delivery cable also provides power output up to 3A (60 watts), which is more than sufficient for charging, syncing and powering compatible devices. The cable is backward compatible with previous USB generations, allowing you to use it with older equipment.

**Reversible USB-C Connector Attaches in Either Direction** Unlike traditional USB cables that connect in only one direction, the reversible USB-C male connector plugs into a USB-C or Thunderbolt 3 port in either direction for a fumble-free connection every time.

### Highlights

- USB-C to USB-A cable is compatible with all USB-C and Thunderbolt 3 devices
- Supports USB 3.1 Gen 2 speeds up to 10 Gbps to ensure lightning-fast data transfers
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- Plug-and-play operation with no software required for easy, immediate installation

### Applications

- Charge and sync a USB-C or Thunderbolt 3 mobile device from a USB-A wall charger or car charger up to 20 in. away
- Transfer data between an external hard drive or flash drive and your computer or laptop
- Connect your desktop computer to a docking station or hub with a USB-C or Thunderbolt 3 port

### System Requirements

- Device with a USB-C or Thunderbolt 3 port
- Device with a USB-A port
- USB 3.1 Gen 2 compatibility required in both connected devices to achieve USB 3.1 Gen 2 speeds

### Package Includes

- U428-20N-G2 USB Type-C to USB Type-A Cable, M/M, 20 in.



## Specifications

OVERVIEW	
UPC Code	037332243423
Technology	USB; USB 3.1 (Gen 1); USB 3.1 (Gen 2)
INPUT	
Cable Length (ft.)	1.7
Cable Length (m)	0.5
Cable Length (in.)	20
Cable Length (cm)	50.8
PHYSICAL	
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	4.5MM
Color	Black
Material of Construction	PVC
Unit Packaging Type	Polybag
ENVIRONMENTAL	
Operating Temperature Range	32 to 113 F (0 to 45 C)
Storage Temperature Range	-40 to 158 F (-40 to 70 C)
Operating Humidity Range	10% to 85%, Non-Condensing
Storage Humidity Range	5% to 90%, Non-Condensing
CONNECTIONS	
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	USB C (MALE)
Connector Plating	Nickel
Contact Plating	Gold
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.1 Gen 2 (up to 10 Gbps)
STANDARDS & COMPLIANCE	
Certifications	Tested to RoHS, REACH
WARRANTY	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Product Warranty Period (Worldwide)	Lifetime limited warranty
--	---------------------------

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>