

4-Port Slim Portable USB-A Hub - USB 3.x (5Gbps), Aluminum Housing

MODEL NUMBER: U360-004-4A-AL



Portable USB hub adds 4 USB-A ports to your laptop, Ultrabook, Chromebook, PC, tablet or other USB device.

Features

USB Hub Connects 4 USB Peripherals to Your Computer or Laptop This USB-A hub allows you to connect up to four USB peripherals to your laptop, Ultrabook, Chromebook, PC, tablet or other USB device. You can expand the potential of your device by connecting USB peripherals that can help you do your job faster, easier and better, such as an external hard drive, keyboard/mouse, power meter and printer.

Connects USB Peripherals and Transfers Data at Fast USB 3.2 Gen 1 Speeds All four USB ports transfer data at speeds up to 5 Gbps, which is 10 times faster than USB 2.0. The USB ports are backward compatible with previous USB generations, so you can continue using older peripherals while getting high-speed performance from new devices.

Ready to Use Right Out of the Package The hub connects to your computer via its built-in USB cable, saving you the expense and effort of buying a cable. The four-port hub requires no software, drivers or external power. The slim aluminum case fits easily into a pocket, briefcase or laptop bag for connecting on the go. The hub is compatible with both Windows and Mac operating systems.

Specifications

OVERVIEW	
UPC Code	037332214003
Product Type	Hub
Device Compatibility	Chromebook; Computer; Laptop
Technology	USB 3.x
Country/Region	Global
Host Connector	USB A (MALE)

Highlights

- Accepts up to 4 USB peripherals, turning your laptop into a mini workstation
- Supports USB 3.2 Gen 1 speeds up to 5 Gbps to ensure fast data transfers
- Slim aluminum housing fits easily into purse or laptop bag for use anywhere
- Plug-and-play operation with no software required for easy, immediate installation

System Requirements

Laptop, Ultrabook, Chromebook, PC, tablet or other device with USB-A connector (USB 3.2 Gen 1 port needed to achieve USB 3.2 Gen 1 speeds)

Package Includes

U360-004-4A-AL 4-Port Slim Portable USB-A Hub



Powering Business Worldwide

TRIPP LITE
SERIES

VIDEO	
Extended Mode	No
Mirror Mode	No
DisplayPort Alt Mode	No
DATA	
Data Ports	(4) USB A (FEMALE)
Data Ports Details	(4) USB-A - USB 3.2 Gen 1 (5 Gbps)
INPUT	
Bus Powered	Yes
Product Length (in.)	8.5
Product Length (cm.)	21.6
Product Length (ft.)	0.71
Product Length (m)	0.22
POWER	
Power Source Type	USB
USB Power Delivery (PD) Charging Support	No
CONNECTIONS	
Number of Ports	4
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	(4) USB A (FEMALE)
Connector Plating	Nickel
Connector Style	Straight
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	(x1) Blue - Power
PHYSICAL	
Color	Black
Material of Construction	Aluminum
Cable Jacket Color	Black
Connector Color	Black
Cable Jacket Material	TPE
Cable Jacket Rating	VW-1



Powering Business Worldwide

TRIPP LITE
SERIES

Cable Outer Diameter (OD)	4.0mm
Cable Length (ft.)	0.66
Cable Length (m)	0.20
Cable Length (in.)	7.87
Cable Length (cm)	20
Total Number of Ports	4
Shipping Dimensions (hwd / in.)	0.79 x 5.95 x 3.15
Shipping Weight (kg)	0.08
Unit Dimensions (hwd / in.)	1.600 x 2.400 x 0.400
Unit Dimensions (hwd / cm)	0.95 x 3.97 x 6.0
Unit Dimensions (hwd / mm)	9.5 x 39.7 x 60
Unit Packaging Type	Box
Unit Weight (lbs.)	0.09
Unit Weight (kg)	0.04
ENVIRONMENTAL	
Operating Temperature Range	32° to 122°F (0° to 50°C)
Storage Temperature Range	14° to 167°F (-10° to 75°C)
Relative Humidity	0% to 85% RH, Non-Condensing
FEATURES & SPECIFICATIONS	
USB Hub Ports	Yes
Number of USB Hub Ports	4
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps); USB 3.2 Gen 1 (up to 5 Gbps)
Data Transfer Rate	(4) 5 Gbps
Driver Required	No
STANDARDS & COMPLIANCE	
TAA Compliant Option	N
Product Compliance	CE (Europe); FCC (USA); REACH; RoHS; UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty



Powering Business Worldwide

TRIPP LITE
SERIES

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.