


7-Port Portable USB 3.0 SuperSpeed Mini Hub, Aluminum

MODEL NUMBER: **U360-007-AL**



Connects to the USB 3.0 port on your laptop, Ultrabook or computer to give you 7 external USB 3.0 ports.

Description

The U360-007-AL 7-Port Portable USB 3.0 SuperSpeed Mini Hub's built-in USB cable connects to your laptop, Ultrabook or computer to provide seven available USB 3.0 ports. Just plug and play with no drivers or software needed. The included external power supply provides 5V 3A to be shared among all seven USB ports, with each port capable of providing up to 1.5A for fast charging of mobile devices. All seven ports support USB Battery Charging (BC) specification v1.2. This portable hub supports USB 3.0 data transfer rates up to 5 Gbps—ten times faster than USB 2.0—and is backward compatible with USB 2.0 and USB 1.1 devices. The compact, lightweight aluminum case fits easily into your pocket, backpack, briefcase or laptop bag.

Features

Increases Your Computer's USB 3.0 Ports from 1 to 7 Expands your laptop, Ultrabook or computer's USB 3.0 port to 7 external USB 3.0 ports
Included external power supply provides 5V 3A to be shared among all ports
Each port is capable of providing up to 1.5A
Supports USB Battery Charging (BC) specification v1.2

Excellent Speed and Versatile Performance Supports USB 3.0 data transfer rates up to 5 Gbps—10 times faster than USB 2.0
Backward compatible with USB 2.0 and USB 1.1

Take the Hub Anywhere Compact case made from lightweight aluminum
Fits easily into your pocket, backpack, briefcase or laptop bag
Built-in cable is perfect for travel

Highlights

- USB ports can provide up to 1.5A for charging mobile devices*
- All seven ports support USB Battery Charging (BC) specification v1.2
- Supports USB 3.0 data transfer rates up to 5 Gbps
- Plug and play—no drivers or software needed
- Fits easily into pocket, backpack, briefcase or laptop bag
- Backward compatible with USB 2.0 and USB 1.1

**When using the included external power supply*

System Requirements

- Device with USB port (USB 3.0 port needed to achieve USB 3.0 speeds)

Package Includes

- U360-007-AL 7-Port Portable USB 3.0 SuperSpeed Mini Hub
- External power supply (Input: 100–240V, 50/60 Hz, 0.6A; Output: 5V 3A)

Specifications

OVERVIEW	
UPC Code	037332201027
Product Type	Hub
AC Adapter	Input: 100-240V, 50/60Hz, 0.6A; Output: 5V, 3A



Host Connector	USB A (MALE)
VIDEO	
Extended Mode	No
Mirror Mode	No
Number of Monitors Supported	0
DATA	
Data Ports	(7) USB A (FEMALE)
Data Ports Detail	(7) USB-A - USB 3.2 Gen 1 (5 Gbps)
INPUT	
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
External Power Supply Input Specs (V / Hz / A)	100-240V / 50/60Hz / 0.6A
External Power Supply Output Specs (V / A)	5V / 3A
External Power Supply Cord Length (ft.)	5
External Power Supply Cord Length (m.)	1.5
External Power Supply DC Barrel Connector Specs	OD: 3.5 x 1.35 x 10mm, Positive Pin, Negative Sleeve
External Power Supply Plug(s)	NEMA 1-15P North America
External Power Supply Certifications	CE; FCC; UL; cUL; TUV; CCC; RoHS
Bus Powered	No
Product Length (in.)	21.6
Product Length (cm.)	54.86
Product Length (ft.)	1.8
Product Length (m.)	0.548
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	White (Power)
CHARGING	
Charging Ports	USB-A: 5V 1.5A (7.5W)
PHYSICAL	
Cable Jacket Rating	VW-1
Color	Black



Material of Construction	Aluminum
Shipping Dimensions (hwd / cm)	5.59 x 11.18 x 19.56
Shipping Dimensions (hwd / in.)	2.20 x 4.40 x 7.70
Shipping Weight (kg)	0.39
Shipping Weight (lbs.)	0.87
Unit Dimensions (hwd / in.)	0.83 x 6.2 x 1.2
Unit Packaging Type	Box
Unit Weight (kg)	0.24
Unit Weight (lbs.)	0.53
ENVIRONMENTAL	
Operating Temperature Range	-4 to 158 F (-20 to 70 C)
Storage Temperature Range	14 to 158 F (-10 to 70 C)
Relative Humidity	10% to 90% RH, Non-Condensing
BTUs	4.7 BTU/Hr
Power Consumption (Watts)	1.4
Power Provided to Connected Device(s)	5V 1.5A (7.5W) Output per USB Port
CONNECTIONS	
Ports	7
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	(7) USB 3.0 A (FEMALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
Technology	USB 3.0 (SuperSpeed); USB
STANDARDS & COMPLIANCE	
Certifications	Tested to CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>