


7-Port Portable USB 3.x (5Gbps) Mini Hub, Aluminum

MODEL NUMBER: **U360-007-AL**



Connects to the USB 3.0 port on your laptop, Ultrabook or computer to give you 7 external USB 3.0 ports.

Description

The U360-007-AL 7-Port Portable USB 3.0 SuperSpeed Mini Hub's built-in USB cable connects to your laptop, Ultrabook or computer to provide seven available USB 3.0 ports. Just plug and play with no drivers or software needed. The included external power supply provides 5V 3A to be shared among all seven USB ports, with each port capable of providing up to 1.5A for fast charging of mobile devices. All seven ports support USB Battery Charging (BC) specification v1.2.

This portable hub supports USB 3.0 data transfer rates up to 5 Gbps—ten times faster than USB 2.0—and is backward compatible with USB 2.0 and USB 1.1 devices. The compact, lightweight aluminum case fits easily into your pocket, backpack, briefcase or laptop bag.

Features

Increases Your Computer's USB 3.0 Ports from 1 to 7 Expands your laptop, Ultrabook or computer's USB 3.0 port to 7 external USB 3.0 ports
 Included external power supply provides 5V 3A to be shared among all ports
 Each port is capable of providing up to 1.5A
 Supports USB Battery Charging (BC) specification v1.2

Excellent Speed and Versatile Performance Supports USB 3.0 data transfer rates up to 5 Gbps—10 times faster than USB 2.0
 Backward compatible with USB 2.0 and USB 1.1

Take the Hub Anywhere Compact case made from lightweight aluminum
 Fits easily into your pocket, backpack, briefcase or laptop bag
 Built-in cable is perfect for travel

Specifications

OVERVIEW	
UPC Code	037332201027
Product Type	Hub
Technology	USB 3.x
Host Connector	USB A (MALE)

Highlights

- USB ports can provide up to 1.5A for charging mobile devices*
- All seven ports support USB Battery Charging (BC) specification v1.2
- Supports USB 3.0 data transfer rates up to 5 Gbps
- Plug and play—no drivers or software needed
- Fits easily into pocket, backpack, briefcase or laptop bag
- Backward compatible with USB 2.0 and USB 1.1

**When using the included external power supply*

System Requirements

- Device with USB port (USB 3.0 port needed to achieve USB 3.0 speeds)

Package Includes

- U360-007-AL 7-Port Portable USB 3.0 SuperSpeed Mini Hub
- External power supply (Input: 100–240V, 50/60 Hz, 0.6A; Output: 5V 3A)

VIDEO	
Number of Monitors Supported	0
Extended Mode	No
Mirror Mode	No
DisplayPort Alt Mode	No
DATA	
Data Ports	(7) USB A (FEMALE)
Data Ports Details	(7) USB-A - USB 3.2 Gen 1 (5 Gbps)
INPUT	
AC Power Adapter Plug(s)	NEMA 1-15P North America
AC Power Adapter Input Specs (V / Hz / A)	100-240V / 50/60Hz / 0.6A
AC Power Adapter Output Specs (V / A)	5V / 3A
AC Power Adapter Cord Length (ft.)	5
AC Power Adapter Cord Length (m)	1.5
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
Bus Powered	No
Product Length (in.)	21.6
Product Length (cm.)	54.86
Product Length (ft.)	1.8
Product Length (m)	0.548
POWER	
Power Source Type	AC Adapter
AC Adapter	Input: 100-240V, 50/60Hz, 0.6A; Output: 5V, 3A
DC Barrel Plug	OD: 3.5 x 1.35 x 10mm, Positive Pin, Negative Sleeve
Power Consumption (Watts)	1.4
CONNECTIONS	
Number of Ports	7
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	(7) USB 3.0 A (FEMALE)
Connector Plating	Nickel
USER INTERFACE, ALERTS & CONTROLS	

LED Indicators	White when connected and powered
CHARGING	
Charging Ports	USB-A: 5V 1.5A (7.5W)
Charging Ports Details	All seven ports support USB Battery Charging v1.2
Charging Ports / Amps	(7) 1.5A
PHYSICAL	
Color	Black
Material of Construction	Aluminum
Cable Jacket Material	TPE
Cable Jacket Rating	VW-1
Shipping Dimensions (hwd / in.)	2.20 x 4.40 x 7.70
Shipping Dimensions (hwd / cm)	5.59 x 11.18 x 19.56
Shipping Weight (lbs.)	0.87
Shipping Weight (kg)	0.39
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Packaging Type	Box
Unit Weight (lbs.)	0.53
Unit Weight (kg)	0.24
ENVIRONMENTAL	
Operating Temperature Range	-4° to 158°F (-20° to 70°C)
Storage Temperature Range	14° to 158°F (-10° to 70°C)
Relative Humidity	10% to 90% RH, Non-Condensing
BTUs	4.7 BTU/Hr
Power Provided to Connected Device(s)	5V 1.5A (7.5W) Output per USB Port
FEATURES & SPECIFICATIONS	
USB Hub Ports	Yes
Number of USB Hub Ports	7
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps); USB 3.2 Gen 1 (up to 5 Gbps)
Driver Required	No
STANDARDS & COMPLIANCE	
TAA Compliant Option	N
External Power Supply Certifications	CE; FCC; UL; cUL; TUV; CCC; RoHS



Powering Business Worldwide



Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.