

USB-C Flat Cable (M/M) - USB 3.1 Gen 2 (10 Gbps), Thunderbolt 3 Compatible, Black, 3 ft. (0.9 m)

MODEL NUMBER: U420-003-G2-FL



Flat USB 3.1 Gen 2 cable connects a smartphone or other USB-C device to the USB-C port on your computer, charger or power bank.

Features

Flat USB-C Cable Transfers Data and Charges Devices at Lightning-Fast USB 3.1 Gen 2

SpeedsThis USB sync/charge cable (M/M) connects your smartphone, tablet, MacBook Pro, Windows laptop or other USB-C device to the USB-C port on a computer, docking station or wall charger. It supports USB 3.1 Gen 2 data transfer rates up to 10 Gbps, which is twice as fast as USB 3.1 Gen 1. It also provides power output up to 2.3 amps (46 watts), which is sufficient for charging and powering most mobile devices.

Innovative Flat Cable Prevents Tangles, Allows Flexible BendsVery flexible for convenient on-the-go connections, this flat cable avoids nasty tangles in your backpack or laptop bag. Its advanced flat design allows easy rolling for tangle-free storage. Plus, it bends easily for connecting to devices in tight spaces or around obstacles.

Reversible USB-C Connectors Attach in Either DirectionUnlike traditional USB cables that connect in only one direction, the reversible USB-C male connectors plug into a USB-C or Thunderbolt 3 port in either direction for an instant connection every time.

Highlights

- Flexible flat design helps prevent inconvenient tangling and allows easy bending
- Supports USB 3.1 Gen 2 speeds up to 10 Gbps to ensure lightning-fast data transfers
- Provides 2.3A (46W) power output for charging, syncing and powering mobile devices
- Reversible USB-C plugs connect in either direction for immediate no-fuss use
- Flat USB-C cable is compatible with all USB-C and Thunderbolt 3 devices

Applications

- Charge and power your MacBook Pro, Windows laptop or other USB-C or Thunderbolt 3 device from a USB-C wall charger
- Transfer data between an external hard drive and your laptop or PC
- Connect your laptop to a docking station or hub with a USB-C or Thunderbolt 3 port
- Carry in your laptop bag, backpack or briefcase as a flexible spare cable

System Requirements

- Devices with USB-C or Thunderbolt 3 ports (USB 3.1 Gen 2 compatibility required to achieve USB 3.1 Gen 2 speeds)

Package Includes



- U420-003-G2-FL Flat USB-C to USB-C Cable, M/M, Black, 3 ft.

Specifications

OVERVIEW	
UPC Code	037332254030
INPUT	
Maximum Input Amps	2.3
Cable Length (ft.)	3
Cable Length (m)	0.9
Cable Length (in.)	36
PHYSICAL	
Cable Jacket Type	TPE
Cable Outer Diameter (OD)	1.2*11.0MM
Color	Black
Material of Construction	TPE
Unit Packaging Type	Polybag
Wire Gauge (AWG)	30
ENVIRONMENTAL	
Operating Temperature Range	14 to 140 F (-10 to 60 C)
Storage Temperature Range	-4 to 158 F (-20 to 70 C)
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	10% to 85% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	USB C (MALE)
Connector Plating	Nickel
Contact Plating	Gold
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.1 Gen 2 (up to 10 Gbps)



Technology	USB 3.1 (Gen 2)
STANDARDS & COMPLIANCE	
Certifications	CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>