

USB-C to HDMI 4K Adapter with USB-A Port and PD Charging, HDCP, White

MODEL NUMBER: **U444-06N-H4U-C**



Adds HDMI, USB-A and USB-C PD ports to the USB-C or Thunderbolt 3 port on your tablet, laptop, notebook, MacBook, Chromebook, smartphone or PC.

Description

The U444-06N-H4U-C USB 3.1 Gen 1 USB-C to HDMI 4K Adapter expands the potential of your tablet, laptop, Chromebook, MacBook, smartphone or PC's USB-C or Thunderbolt 3 port. It's ideal for transmitting digital audio and 4K video to a large display, adding a thumb drive or other USB peripheral, and powering and charging a PD Charging-compliant mobile device—all at the same time.

With a source device that also supports USB DisplayPort Alternate Mode, you can extend video from your primary display to another, duplicate the same video on both displays, or change the second display to your primary.

The plug-and-play U444-06N-H4U-C requires no software, drivers or external power. Connect the reversible USB-C plug to your source device's USB-C or Thunderbolt 3 port. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time.

To send digital audio and HD video to an HDMI television, projector or monitor, connect the HDMI port to the display using an HDMI cable (sold separately). The HDMI port supports UHD video resolutions up to 3840 x 2160 (4K x 2K) at 30 Hz.

The USB-A port accepts USB peripherals, such as a flash drive, mouse, keyboard or printer. It supports fast USB 3.1 Gen 1 data transfer rates up to 5 Gbps and is backward compatible with previous USB generations. The port provides up to 5V/1.5A (7.5W) of fast charging power to mobile devices.

Along with data transfer, the USB-C Power Delivery (PD) port provides power and charging to the PD Charging-compliant device (such as a MacBook or Chromebook) the U444-06N-H4U-C is connected to. Connect the device's AC wall charger to the USB-C PD port, which supports power input up to 20V 3A (60W).

Features

Turn Your Device's USB-C Port into a Multiport Workstation

- Ideal for transmitting audio/video to a large display, adding a USB peripheral, and powering and charging a PD Charging-compliant mobile device simultaneously
- Plug-and-play operation with no software, drivers or external power required

Highlights

- Supports USB DisplayPort Alternate Mode for transmitting audio/video
- Supports UHD video resolutions up to 3840 x 2160 (4K x 2K) @ 30 Hz
- USB-C port supports both data transfer and USB Power Delivery (PD) charging with power input up to 20V 3A (60W)
- USB-A port provides up to 5V/1.5A (7.5W) of fast-charging power
- Reversible USB-C plug connects in either direction
- Plug-and-play operation with no software or drivers required

System Requirements

- Source device with USB-C or Thunderbolt 3 port that supports USB DisplayPort Alternate Mode
- Display device with HDMI input (HDMI port)

Package Includes

- U444-06N-H4U-C USB 3.1 Gen 1 USB-C to HDMI 4K Adapter
- Owner's manual



- About the size of a credit card for easy carrying in a pocket, purse or laptop bag
- Transmit Crystal-Clear 4K Video and Digital Audio to HDMI Display**
- Compatible with USB-C or Thunderbolt 3 source devices that support USB DisplayPort Alternate Mode
 - Supports HD video resolutions up to 3840 x 2160 (4K x 2K) @ 30 Hz
 - Extends video from your primary display to another
 - Duplicates the same video on 2 displays
 - Converts a secondary display to your primary display

Connect a USB Peripheral

- USB-A port accepts flash drives, mice, keyboards, printers and other USB peripherals
- Supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps
- Backward compatible with USB 2.0 and USB 1.1
- Provides up to 5V/1.5A (7.5W) of fast-charging power to mobile devices

Note: Host must support USB OTG (On-the-Go)

Charge a Connected Device

- USB-C PD port connects to wall charger to power and charge the connected PD Charging-compliant USB-C/Thunderbolt 3 device
- Supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps
- Supports power input up to 20V 3A (60W)

- USB-C port also supports data transfer

Note: USB-C PD port does not support Quick Charge (QC).

Built-In Cable with Reversible USB-C Connector

- Fumble-free reversible USB-C plug connects in either direction for quick connection every time

Specifications

| OVERVIEW | |
|--------------------------------|---|
| UPC Code | 037332193957 |
| Technology | USB 3.1 (Gen 1); HDMI; USB; PD Charging |
| VIDEO | |
| Max Supported Video Resolution | HDMI: 3840 X 2160 (4K X 2K) @ 30HZ |
| INPUT | |
| Bus Powered | Yes |
| Product Length (in.) | 6 |
| Product Length (cm.) | 15.24 |
| Product Length (ft.) | 0.5 |
| Product Length (m.) | 0.15 |
| BATTERY | |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|--|-------------------------------|
| Battery Charging (5V/1.5A Port) | Yes |
| POWER | |
| USB Power Delivery (PD) Charging Support | Yes |
| USB Power Delivery (PD) Charging Specification | 2.0 |
| CHARGING | |
| Charging Ports / Amps | 1.5A; 3A |
| Total Charging Watts | 60 |
| PHYSICAL | |
| Color | White |
| Cable Jacket Rating | VW-1 |
| Material of Construction | PVC, ABS |
| Shipping Dimensions (hwd / cm) | 2.29 x 9.91 x 12.19 |
| Shipping Dimensions (hwd / in.) | 0.90 x 3.90 x 4.80 |
| Shipping Weight (kg) | 0.09 |
| Shipping Weight (lbs.) | 0.20 |
| Unit Dimensions (hwd / cm) | 1.4 x 4 x 5.9 |
| Unit Dimensions (hwd / in.) | 0.55 x 1.57 x 2.32 |
| Unit Packaging Type | Box |
| Unit Weight (kg) | 0.03 |
| Unit Weight (lbs.) | 0.07 |
| ENVIRONMENTAL | |
| Operating Temperature Range | 32 to 113 F (0 to 45 C) |
| Storage Temperature Range | 14 to 158 F (-10 to 70 C) |
| BTUs | 5.1 BTU/Hr |
| Power Consumption (Watts) | 1.5 |
| Operating Humidity Range | 10% to 85% RH, Non-Condensing |
| Storage Humidity Range | 5% to 90% RH, Non-Condensing |
| CONNECTIONS | |
| Ports | 3 |
| Side A - Connector 1 | USB C (MALE) |
| Side B - Connector 1 | HDMI (FEMALE) |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|--------------------------------------|--|
| Side B - Connector 2 | USB 3.0 A (FEMALE) |
| Side B - Connector 3 | USB Type-C (FEMALE) |
| Connector Plating | Nickel |
| FEATURES & SPECIFICATIONS | |
| HDCP Specification | 1.4 |
| USB Specification | USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps) |
| Driver Required | No |
| STANDARDS & COMPLIANCE | |
| Certifications | Tested to CE, FCC, RoHS, REACH |
| WARRANTY | |
| Product Warranty Period (Worldwide) | 3-year limited warranty |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>