

## USB-C to USB Type-B Cable (M/M) - USB 3.1, Gen 2 (10 Gbps), Thunderbolt 3 Compatible, 20-in.

MODEL NUMBER: U422-20N-G2



Connects a printer, hub or other USB-B device to your laptop, MacBook, Chromebook or Ultrabook's USB-C or Thunderbolt 3 port.

### Features

**Connects a USB-B Printer, Scanner or External Hard Drive to Your Laptop's USB-C Port** This USB-C to USB 3.0 Type-B cable allows you to connect a printer, scanner, hard drive, docking station, optical drive or other existing USB-B peripheral to any device with a USB-C or Thunderbolt 3 port, including MacBooks, Ultrabooks and Chromebooks. Its 20-inch length makes it easy to carry in your briefcase or laptop bag for quick downloads and file transfers on the go.

**Transfers Data and Charges Devices at Lightning-Fast USB 3.1 Gen 2 Speeds** The USB Type-C to USB 3.0 Type-B cable supports USB 3.1 Gen 2 data transfer rates up to 10 Gbps, which is double the speed of USB 3.1 Gen 1.

**Reversible USB-C Connector Attaches in Either Direction** Unlike traditional USB cables that connect in only one direction, the reversible USB-C male connector plugs into a USB-C or Thunderbolt 3 port in either direction for a fumble-free connection every time.

### Highlights

- USB-C to USB 3.0 Type-B cable compatible with USB-B, USB-C and Thunderbolt 3 devices
- Supports USB 3.1 Gen 2 speeds up to 10 Gbps to ensure lightning-fast data transfers
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- Plug-and-play operation with no software required for easy, immediate installation

### Applications

- Connect a printer or scanner to the USB-C or Thunderbolt 3 port on your computer or laptop
- Charge and sync a USB-C or Thunderbolt 3 mobile device from a USB-B wall charger up to 20 in. away
- Connect your laptop to a docking station or hub with a USB-B port

### System Requirements

- Devices with USB-C or Thunderbolt 3 ports
- Devices with USB-B ports
- USB 3.1 Gen 2 compatibility required in both connected devices to achieve USB 3.1 Gen 2 speeds

### Package Includes

- U422-20N-G2 USB-C 3.1 Gen 2 to USB 3.0 Type-B Cable (M/M), 20 in.



## Specifications

OVERVIEW	
UPC Code	037332243416
INPUT	
Cable Length (ft.)	1.7
Cable Length (m)	0.5
Cable Length (in.)	20
Cable Length (cm)	50.8
PHYSICAL	
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	4.5MM
Color	Black
Material of Construction	PVC
Unit Packaging Type	Polybag
ENVIRONMENTAL	
Operating Temperature Range	14 to 140 F (-10 to 60 C)
Storage Temperature Range	-4 to 185 F (-20 to 85 C)
Relative Humidity	10 to 85% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	USB B (MALE)
Connector Plating	Nickel
Contact Plating	Gold
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.1 Gen 2 (up to 10 Gbps)
Technology	USB; USB 3.0 (SuperSpeed); USB 3.1 (Gen 1); USB 3.1 (Gen 2)
STANDARDS & COMPLIANCE	
Certifications	Tested to RoHS, REACH



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>