



USB 3.1 Gen 1 USB-C Multi-Drive Smart-Card Flash-Memory Media Reader/Writer, Thunderbolt™ 3 Compatible

MODEL NUMBER: U452-003









Transfer data between your tablet, laptop, Ultrabook, Chromebook or computer and a wide variety of memory cards via the USB-C or Thunderbolt™ 3 port on your electronic device.

Description

If your tablet, laptop, Ultrabook, Chromebook or computer doesn't have a built-in memory card reader, but does have a USB Type-C or ThunderboltTM 3 port, the U452-003 USB 3.1 Gen 1 Multi-Drive Smart-Card Flash-Memory Media Reader/Writer can easily transfer data between your device and a wide variety of memory cards.

Photo libraries, documents, high-definition audio and video, and other large files transfer at USB 3.1 Gen 1 speeds up to 5 Gbps. Backward compatible with previous USB generations, so data can still transfer regardless of your device. The compact aluminum case with built-in 3-ft. (0.91 m) USB-C cable fits easily into your pocket, backpack, briefcase or laptop bag so you can read and write files at a moment's notice. No drivers or external power supply needed.

Supporting the latest industry standards, the U452-003 is compatible with a wide range of SD (Secure Digital), Micro SD and CF (CompactFlash) memory cards, including:

- SD Cards: Secure Digital (SD), Elite Pro SD, Extreme III SD, Gaming Edition SD, Platinum II SD, SD Pro, SDHC, SDXC, SD-Max, SD-Pleomax, SD-Pro C, Super SD, Turbo SD, Ultima I SD, Ultima II SD, Ultimate SD, Ultra High Speed SD, Ultra II SD, Ultra II SD Plus, Ultra SD, Ultra-X SD, DV-RS MMC, High Speed MMC / RS-MMC, MCCmobile, MMC Pro, MMCplus, MMCplus Turbo, RS-MMC
- Micro SD Cards: MicroSD (TransFlash), microSDHC / M2
- CF Cards: CompactFlash Type I/II, CF Elite Pro, CF PRO I, CF PRO II, CF Turbo, CF Ultima I, CF Ultima II, Extreme CF, Extreme III CF, HS CF, Ultra II CF

USB Type-C™ and USB-C™ are trademarks of USB Implementers Forum

Features

High-Speed Data Transfer

- Ideal for transferring photos, documents, hi-def audio and video, and other files between memory card and your tablet, laptop, Ultrabook, Chromebook or computer
- Supports the connection of one memory card at a time
- Built-in 3-ft. (0.91 m) USB-C cable connects to device's USB-C or Thunderbolt™ 3 port
- Supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps
- · Backward compatible with previous USB generations

Highlights

- Supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps
- Backward compatible with previous USB generations
- Compatible with all USBenabled operating systems
- Plug and play—no drivers or external power supply needed
- Fits easily into pocket, backpack, briefcase or laptop bag

System Requirements

- Tablet, laptop, Ultrabook, Chromebook or computer with USB-C or Thunderbolt™ 3 port (USB 3.1 port required for USB 3.1 speeds)
- Supports the connection of one memory card at a time

Package Includes

 U452-003 USB 3.1 Gen 1 Multi-Drive Smart-Card Flash-Memory Media Reader/Writer





Plug-and-Play Convenience

- No drivers or external power supply necessary
- Compact case made from lightweight aluminum
- Fits easily into your pocket, backpack, briefcase or laptop bag
- Compatible with all USB-enabled operating systems

Compatible with Wide Range of Memory Cards

- SD Cards: Secure Digital (SD), Elite Pro SD, Extreme III SD, Gaming Edition SD, Platinum II SD, SD Pro, SDHC, SDXC, SD-Max, SD-Pleomax, SD-Pro C, Super SD, Turbo SD, Ultima I SD, Ultima II SD, Ultimate SD, Ultra High Speed SD, Ultra II SD, Ultra II SD Plus, Ultra SD, Ultra-X SD, DV-RS MMC, High Speed MMC / RS-MMC, MCCmobile, MMC Pro, MMCplus, MMCplus Turbo, RS-MMC
- Micro SD Cards: MicroSD (TransFlash), microSDHC / M2
- CF Cards: CompactFlash Type I/II, CF Elite Pro, CF PRO I, CF PRO II, CF Turbo, CF Ultima I, CF Ultima II, Extreme CF, Extreme III CF, HS CF, Ultra II CF

Specifications

OVERVIEW		
UPC Code	037332190192	
INPUT		
Bus Powered	Yes	
Product Length (in.)	6	
Product Length (cm.)	15.24	
Product Length (ft.)	0.5	
Product Length (m)	0.15	
BATTERY		
Battery Charging (5V/1.5A Port)	No	
POWER		
Power Consumption (Watts)	0.77	
CONNECTIONS		
Number of Ports	3	
Side A - Connector 1	USB C (MALE)	
Side B - Connector 1	SD (FEMALE)	
Side B - Connector 2	MICRO SD (FEMALE)	
Side B - Connector 3	CF (FEMALE)	
Connector Plating	Nickel	
PHYSICAL		





Color	Silver; White	
Material of Construction	Aluminum	
Cable Jacket Rating	VW-1	
Cable Length (ft.)	0.92	
Cable Length (m)	0.28	
Shipping Dimensions (hwd / in.)	1.20 x 4.90 x 3.90	
Shipping Dimensions (hwd / cm)	3.05 x 12.45 x 9.91	
Shipping Weight (lbs.)	0.22	
Shipping Weight (kg)	0.10	
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000	
Unit Packaging Type	Вох	
Unit Weight (lbs.)	0.16	
Unit Weight (kg)	0.07	
3 (3/		
ENVIRONMENTAL		
Operating Temperature Range	-4° to 158°F (-20° to 70°C)	
Storage Temperature Range	-4° to 185°F (-20° to 85°C)	
Relative Humidity	15% to 85% RH, Non-Condensing	
BTUs	2.6 BTU/Hr	
FEATURES & SPECIFICATIONS		
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)	
IP68 Rated	No	
IP20 Rated	No	
UASP Support	No	
Auto MDIX Support	No	
Full Duplex Support	No	
Suspend Mode Support	No	
Remote Wakeup Support	No	
SD Card Specification	SD; Micro SD	
Driver Required	No	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)	
WADDANITY & CURRORT		
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	3-year limited warranty	





1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.