

3-Port USB-C Hub with Card Reader, USB-C to 3x USB-A Ports and SD Reader, USB 3.0, White

MODEL NUMBER: U460-003-3AM



Adds 3 USB-A ports and memory card slots to the USB-C or Thunderbolt 3 port on your MacBook, Chromebook, tablet or notebook.

Features

USB-C 3.1 Hub Connects USB Peripherals to Your USB-C or Thunderbolt 3 Device

This USB-C hub allows you to connect up to three USB peripherals to your tablet, laptop, notebook, MacBook, Chromebook, smartphone or PC. This lets you expand the potential of your device by connecting USB peripherals, such as an external hard drives, flash drives, power meters and printers. You can also insert a memory card into the corresponding slot to transfer data. The memory card reader supports MicroSD, SD, SDHC, SDXC and MMC cards for convenient access to digital photos, camcorder videos, smartphone data and other essential files. Only one memory card may be used at a time.

Connects USB Peripherals and Transfers Data at Fast USB 3.1 Gen 1 Speeds

In addition to accepting USB peripherals, the USB ports provide up to 0.9 amps each for charging and powering smartphones and other mobile devices. All three USB ports and the memory card slot transfer data at speeds up to 5 Gbps, which is 10 times faster than USB 2.0. The USB ports are backward compatible with previous USB generations, so you can continue using older peripherals while getting high-speed performance from new devices.

Built-In USB-C Cable Connects in Either Direction

Connect the reversible USB-C plug to your source device's USB-C or Thunderbolt 3 port. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time.

Ready to Use Right Out of the Package

The plug-and-play USB Type-C hub is specifically designed for use with the MacBook, Google Chromebook Pixel and other laptops, tablets and devices equipped with a USB-C or Thunderbolt 3 port. It requires no software, drivers or external power. It's about the size of a credit card to make it easy to carry in a pocket, backpack or laptop bag for use anywhere.

Highlights

- USB-C 3.1 Type-C hub is compatible with all USB-C and Thunderbolt 3 devices
- Connects external hard drives, keyboard, printer and other USB peripherals
- Supports USB 3.1 Gen 1 speeds up to 5 Gbps to ensure fast data transfers
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- Plug-and-play operation with no software required for easy, immediate installation

Applications

- Charge and power a tablet, smartphone or other compatible mobile device
- Connect up to 3 USB peripherals, such as an external hard drive, flash drive and printer
- Transfer photos, videos and other important files between your MacBook or Chromebook and a memory card

System Requirements

- Device with USB-C or Thunderbolt 3 port (USB 3.1 port needed to achieve USB 3.1 speeds)

Package Includes

- U460-003-3AM USB 3.1 Gen 1 USB-C Hub, 5 Gbps, White
- Owner's manual



Specifications

OVERVIEW	
UPC Code	037332193766
Product Type	Hub
Technology	USB 3.0 (SuperSpeed); USB 3.1 (Gen 1); USB
Host Connector	USB C (MALE)
VIDEO	
Extended Mode	No
Mirror Mode	No
Number of Monitors Supported	0
DATA	
Data Ports	(3) USB A (FEMALE)
Data Ports Detail	(3) USB-A - USB 3.2 Gen 1 (5 Gbps)
STORAGE	
Card Slots	SD (FEMALE); MICRO SD (FEMALE)
Card Slots Detail	SD 3.0 Memory Card slots (SD and MicroSD)
INPUT	
Bus Powered	Yes
Product Length (in.)	6
Product Length (cm.)	15.24
Product Length (ft.)	0.5
Product Length (m.)	0.15
BATTERY	
Battery Charging (5V/1.5A Port)	No
CHARGING	
Charging Ports / Amps	(3) 0.9A
PHYSICAL	
Cable Jacket Rating	VW-1
Color	White



Material of Construction	Plastic
Shipping Dimensions (hwd / in.)	0.90 x 4.00 x 5.60
Shipping Weight (lbs.)	0.16
Unit Dimensions (hwd / in.)	0.43 x 3.7 x 1.6
Unit Packaging Type	Box
Unit Weight (kg)	0.05
Unit Weight (lbs.)	0.11
ENVIRONMENTAL	
Operating Temperature Range	32 to 113 °F (0 to 45 °C)
Storage Temperature Range	14 to 158 °F (-10 to 70 °C)
BTUs	8.2
Power Consumption (Watts)	2.4
Operating Humidity Range	10 - 85 % RH
Storage Humidity Range	5 - 90 % RH
CONNECTIONS	
Ports	5
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	(3) USB 3.0 A (FEMALE)
Side B - Connector 2	MICRO SD (FEMALE)
Side B - Connector 3	SD (FEMALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
UASP Support	Yes
SD Card Specification	SD; Micro SD
STANDARDS & COMPLIANCE	
Certifications	CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>