

## 3-Port USB-C Hub with Card Reader, USB-C to 3x USB-A Ports and SD Reader, USB 3.0, Black

MODEL NUMBER: **U460-003-3AMB**



Adds 3 USB-A ports and 2 memory card slots to the USB-C or Thunderbolt 3 port on your tablet, laptop, notebook, MacBook, Chromebook, smartphone or PC.

### Description

The U460-003-3AMB USB 3.1 Gen 1 USB-C Portable Hub/Adapter expands the potential of your tablet, laptop, MacBook, Chromebook, smartphone or PC's USB-C or Thunderbolt 3 port. It's ideal for adding a thumb drive and other USB peripherals, charging a mobile device, and accessing data on a memory card—all at the same time.

The plug-and-play U460-003-3AMB requires no software, drivers or external power. Connect the reversible USB-C plug to your source device's USB-C or Thunderbolt 3 port. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time.

Three USB-A ports accept USB peripherals, such as a flash drive, mouse, keyboard or printer, and each provides up to 0.9A for charging smartphones and other mobile devices. All ports support fast USB 3.1 Gen 1 data transfer rates up to 5 Gbps and are backward compatible with previous USB generations, so you can continue using older peripherals while getting high-speed performance from new devices.

The memory card slots support MicroSD, SD, SDHC, SDXC and MMC cards for convenient access to digital photos, camcorder videos, smartphone data and other essential files.

### Features

**Turn Your Device's USB-C Port into a Multiport Workstation** Ideal for adding USB peripherals, powering a mobile device and accessing memory card data simultaneously  
Plug-and-play operation with no software, drivers or external power required  
About the size of a credit card for easy carrying in a pocket, purse or laptop bag

**Connect USB Peripherals** 3 USB-A ports accept flash drives, mice, keyboards, printers and other USB peripherals  
Each port provides up to 0.9A for charging mobile devices  
Supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps  
Backward compatible with USB 2.0 and USB 1.1

Note: Host must support USB OTG (On-the-Go)

**Access Memory Card Files** Card reader supports MicroSD, SD, SDHC, SDXC and MMC memory cards for convenient access to photos, videos and other data

**Built-In Cable with Reversible USB-C Connector** Fumble-free reversible USB-C plug connects in either direction for quick connection every time

### Highlights

- Supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps
- USB-A ports provide up to 0.9A each for charging devices
- Compact and easy to carry in a pocket, purse or laptop bag
- Reversible USB-C plug connects in either direction
- Plug-and-play operation with no software or drivers required

### System Requirements

- Source device with USB-C or Thunderbolt 3 port (USB 3.1 port needed to achieve USB 3.1 speeds)

### Package Includes

- U460-003-3AMB USB 3.1 Gen 1 USB-C Portable Hub/Adapter, Black
- Owner's manual

## Specifications

<b>OVERVIEW</b>	
UPC Code	037332209191
Product Type	Hub
Host Connector	USB C (MALE)
<b>VIDEO</b>	
Number of Monitors Supported	0
Extended Mode	No
Mirror Mode	No
<b>DATA</b>	
Data Ports	(3) USB A (FEMALE)
Data Ports Details	(3) USB-A - USB 3.2 Gen 1 (5 Gbps)
<b>STORAGE</b>	
Card Slots	SD (FEMALE); MICRO SD (FEMALE)
Card Slots Details	SD 3.0 Memory Card slots (SD and MicroSD)
<b>INPUT</b>	
Bus Powered	Yes
Product Length (in.)	6
Product Length (cm.)	15.24
Product Length (ft.)	0.5
Product Length (m.)	0.15
<b>BATTERY</b>	
Battery Charging (5V/1.5A Port)	No
<b>POWER</b>	
Power Consumption (Watts)	2.4
<b>CHARGING</b>	
Charging Ports / Amps	(3) 0.9A
<b>PHYSICAL</b>	
Color	Black

Material of Construction	Plastic
Cable Jacket Rating	VW-1
Shipping Dimensions (hwd / in.)	0.91 x 5.51 x 3.94
Shipping Weight (lbs.)	0.12
Unit Dimensions (hwd / in.)	0.430 x 3.700 x 1.600
Unit Packaging Type	Box
Unit Weight (lbs.)	0.11
Unit Weight (kg)	0.05
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	14° to 158°F (-10° to 70°C)
Relative Humidity	5% to 90% RH, Non-Condensing
BTUs	8.2
Power Provided to Connected Device(s)	5V 0.9A (4.5W) Output per USB port
<b>CONNECTIONS</b>	
Number of Ports	5
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	(3) USB 3.0 A (FEMALE)
Side B - Connector 2	MICRO SD (FEMALE)
Side B - Connector 3	SD (FEMALE)
Connector Plating	Nickel
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
UASP Support	Yes
Auto MDIX Support	No
Full Duplex Support	No
Suspend Mode Support	No
Remote Wakeup Support	No
SD Card Specification	SD; Micro SD
Driver Required	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)

**WARRANTY & SUPPORT**

Product Warranty Period  
(Worldwide)

3-year limited warranty