

USB-C to 3.5 mm Stereo Audio Adapter - USB 3.1 Gen 1 (5 Gbps), PD 3.0, Silver

MODEL NUMBER: U437-001-C



Connects stereo headphones or a microphone plus a USB wall charger to the USB-C port on your MacBook Pro or Windows laptop.

Features

3.5 mm Audio Adapter Connects to Your Computer's USB-C PortThis USB Type-C to Stereo Audio Adapter allows you to connect a stereo microphone, earbuds, headphones or speakers to your MacBook Pro, Windows laptop, Chromebook or other device with a USB-C port. Not only does this adapter allow you to bypass a defective sound card or 3.5 mm headphone jack, it also lets you connect to a device that offers only USB-C ports. The adapter converts digital high-resolution audio to analog to maintain a crisp, lively sound.

PD Charging Port Charges Connected Device via AC Wall ChargerThe USB-C Power Delivery port supports power output up to 20V 3A (60W), which is sufficient for charging the connected source device more quickly than other chargers. Just connect the device's AC wall charger to the USB-C PD port. By connecting both the USB-C PD and 3.5 mm audio ports at the same time, you can listen to your tunes or record a podcast without using precious battery power.

Built-In USB-C Cable Attaches in Either DirectionUnlike traditional USB cables that connect in only one direction, the reversible USB-C male connector plugs into a USB-C port in either direction for a fumble-free connection every time.

Ready to Use Right Out of the PackageThe plug-and-play audio adapter requires no software or external power. The compact aluminum housing fits easily into a pocket, briefcase or laptop bag for connecting on the go.

Highlights

- Adds a 3.5 mm headphone/mic port to a device that comes without a stereo audio jack
- USB-C PD 3.0 port supports 20V 3A (60W) power output for charging connected device
- Compact aluminum housing fits into a laptop bag for easy listening anywhere
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- Plug-and-play operation with no software required for speedy installation

Applications

- Listen to streaming music or sporting events through headphones, earbuds or speakers
- Connect a microphone to chat online via Skype or Zoom
- Record a podcast on your MacBook, Chromebook or smartphone
- Charge a smartphone, tablet or other USB-C device while making a call or listening to music

System Requirements

- Source device with USB-C port that supports USB digital audio
- Microphone, headphones, earbuds and/or speakers with 3.5 mm plug
- Windows 10, Mac OS 8.6 or



above, Linux, Chrome OS or
Android operating system

Package Includes

- U437-001-C USB-C to Stereo
Audio Adapter, Silver
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332253903
INPUT	
Cable Length (ft.)	0.295
Cable Length (m)	0.09
Built-In Cable Length (ft.)	0.295
Built-In Cable Length (m)	0.09
Built-In Cable Length (in.)	3.54
Bus Powered	Yes
Product Length (in.)	6.20
Product Length (cm.)	15.75
Product Length (ft.)	0.516
Product Length (m.)	0.157
BATTERY	
Battery Charging (5V/1.5A Port)	Yes
CHARGING	
Charging Ports / Amps	3A
USB Power Delivery (PD) Charging Support	Yes
Total Charging Watts	60
USB Power Delivery (PD) Charging Specification	3.0
PHYSICAL	



Cable Jacket Type	TPE
Cable Outer Diameter (OD)	3.2 mm
Color	Silver
Material of Construction	Polycarbonate, ABS, Aluminum
Shipping Dimensions (hwd / in.)	0.78 x 4.72 x 3.94
Shipping Weight (lbs.)	0.79
Unit Dimensions (hwd / in.)	0.374 x 1.751 x 1.141
Unit Packaging Type	Box
Unit Weight (kg)	0.02
Unit Weight (lbs.)	0.05
ENVIRONMENTAL	
Operating Temperature Range	32 to 113 °F (0 to 45 °C)
Storage Temperature Range	14 to 158 °F (-10 to 70 °C)
Operating Humidity Range	10 - 85 %, RH, Non-Condensing
Storage Humidity Range	5 - 90 %, RH, Non-Condensing
Power Provided to Connected Device(s)	20V / 3A (60W)
CONNECTIONS	
Ports	2
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	USB C (FEMALE)
Side B - Connector 2	3.5MM (FEMALE)
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.1 Gen 1 (up to 5 Gbps)
Audio Specification	Digital Hi-Res Audio
Quick Charge Compliant	2.0
Technology	PD Charging; Stereo Audio
STANDARDS & COMPLIANCE	
Certifications	RoHS, REACH, CE, FCC, WEEE
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>