

Portable Charger - USB-A, 5200mAh Power Bank, Lithium-Ion, LED Flashlight, Black

MODEL NUMBER: UPB-05K2-1U



Charge your mobile device anywhere, anytime without plugging into an AC power outlet. Ideal for cellphones, smartphones, tablets, e-readers, MP3 players and Bluetooth speakers, headsets and headphones.

Description

No more frantic searching for an AC power outlet when your cellphone, tablet, or other mobile device's battery power is getting low. The UPB-05K2-1U Portable 5200mAh Mobile Power Bank is the perfect power solution when you're on the road, or stuck somewhere without convenient electricity. It fits comfortably in your pocket, purse, backpack or laptop bag to keep your e-reader, MP3 player, handheld game console or Bluetooth device operating when you need it. Just connect your device to the UPB-05K2-1U's USB-A port using the included USB Micro-B cable or another cable suitable for your device. Press the button to illuminate the LEDs that indicate the Mobile Power Bank's battery capacity at a glance. Press the button and hold for 3-4 seconds to use the device as an LED flashlight. The portable UPB-05K2-1U provides up to 5V, 1A of power, and its 5200mAh capacity charges devices at maximum power up to 5.2 hours. It protects against short circuits, overvoltage, over-current, overcharges and overdischarges. Charge the Mobile Power Bank by connecting its USB Micro-B port to a USB charger or a computer's USB-A port using the included cable. Press the button, and the four LEDs will blink or light solid in various combinations to indicate the battery level.

Features

Travel-Sized for Convenient Charging Anywhere

- Fits comfortably in your pocket, purse, backpack, or laptop bag
- Ideal for charging cellphones, tablets, e-readers, MP3 players, handheld game consoles and Bluetooth headsets, headphones and speakers
- USB Micro-B charging cable included

Superior Charge Capability Without an AC Power Outlet

- Connect USB-A port to device for charging at maximum output up to 5.2 hr.
- Provides up to 5V, 1A of power at 5200mAh capacity
- Protects against short circuits, overvoltage, over-current, overcharges and overdischarges

Built-In Lithium-Ion Battery

- Connect the power bank's USB Micro-B port to a USB charger or a computer's USB-A port to charge

Highlights

- Fits comfortably in your pocket, purse, backpack or laptop bag
- Provides up to 5V, 1A for charging mobile devices
- LEDs indicate remaining battery capacity
- Charges devices at maximum output up to 5.2 hr.
- Includes USB Micro-B charging cable

Package Includes

- UPB-05K2-1U Portable 5200mAh Mobile Power Bank USB Battery Charger
- USB Micro-B cable, 3 ft.
- Owner's Manual



internal battery

- Built-in LEDs indicate how much battery capacity is left
- Device also functions as a convenient LED flashlight

Specifications

OVERVIEW	
UPC Code	037332189370
Product Type	Portable Charger
Charging Form Factor	Portable
Device Compatibility	Phone; Tablet; Amazon Kindle
INPUT	
Nominal Input Voltage(s) Supported	5V DC
Input Plug Type	USB-C (FEMALE)
Input Plug Type Details	USB-A to USB-C cable provided
OUTPUT	
Overload Protection	Yes
CHARGING	
Number of Charging Ports	1
Total Charging Amps	1A
Total Charging Watts	5
Charging Method	USB
Charging Port Type	USB A (FEMALE)
Charging Ports Details	USB-A: 5V 1A (5W)
Charging Ports / Amps	(1) 1A
Charging Method Detail	5,200 mAh
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	1.80 x 5.20 x 5.90
Shipping Dimensions (hwd / cm)	4.57 x 13.21 x 14.99
Shipping Weight (lbs.)	0.54
Shipping Weight (kg)	0.24
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000



Unit Dimensions (hwd / cm)	2.3 x 4.5 x 9.6
Unit Weight (lbs.)	0.26
Unit Weight (kg)	0.12
ENVIRONMENTAL	
Operating Temperature Range	32F to 113F (0C to 45C)
Storage Temperature Range	5F to 140F (-15C to 60C)
CONNECTIONS	
Side A - Connector 1	USB A (FEMALE)
Side B - Connector 1	USB 3.0 MICRO-B (FEMALE)
FEATURES & SPECIFICATIONS	
Overcurrent Protection	Yes
Overvoltage Protection	Yes
GaN Technology	No
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>