

USB-C to VGA Adapter

MODEL NUMBER: U444-06N-VGA



Connects your existing VGA TV, monitor or projector to the USB-C or Thunderbolt 3 port on your tablet, laptop, notebook, MacBook, Chromebook, smartphone or PC.

Description

The U444-06N-VGA USB 3.1 Gen 1 USB-C to VGA Adapter (M/F) helps you transmit 1080p video from your tablet, laptop, Chromebook, MacBook, smartphone or PC to a VGA-enabled television, monitor or projector. It's an ideal tool for giving video presentations in conference rooms and classrooms, editing multiple documents on a larger screen or streaming video for digital signage in crystal-clear 1080p. You can extend video from your primary display to another, duplicate the same video on both displays or change the second display to your primary.

Connect the reversible USB-C plug to your source device's USB-C or Thunderbolt 3 port. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time. Then, connect the VGA port to your display using a VGA cable (sold separately).

The U444-06N-VGA adapter supports HD video resolutions up to 1920x1200 (including 1080p) at 60 Hz and USB 3.1 Gen 1 data transfer rates up to 5 Gbps. You can use up to six adapters to connect six additional displays to a Windows device at the same time.

Features

Connects a VGA Display to Your USB-C or Thunderbolt 3 Device Ideal for giving video presentations, editing multiple documents or streaming video for digital signage
Supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps Compatible with Windows and Mac computers
Add up to 6 adapters to connect 6 displays to a Windows source device

Common Applications Extends video from your primary display to another
Duplicates the same video on 2 displays
Converts a secondary display to your primary display

Crystal-Clear 1080p Video Supports HD video resolutions up to 1920x1200 (including 1080p) @ 60 Hz
Resumes automatically from hibernation and suspend modes

Built-In Cable with Reversible USB-C Connector Fumble-free reversible USB-C plug connects in either direction for quick connection every time

Ready for Instant Use Driver CD included for device compatibility
About the size of a credit card for easy carrying in a pocket, purse or laptop bag
Backward compatible with non-1080p displays

Highlights

- Supports HD video resolutions up to 1920x1200 (1080p) @ 60 Hz
- Supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps
- Automatic wake from hibernation and suspend modes
- Reversible USB-C plug connects in either direction
- Driver CD included for device compatibility

System Requirements

- Source device with USB-C or Thunderbolt 3 port
- Windows 7 and later or Mac OS X 10.8.5 and later (32- and 64-bit versions)
- Also supports Surface tablets running non-RT Windows 8 or 8.1
- Display device with VGA input

Package Includes

- U444-06N-VGA USB 3.1 Gen 1 USB-C to VGA Adapter (M/F)
- Driver CD
- Owner's manual

Specifications



Powering Business Worldwide



OVERVIEW	
UPC Code	037332189318
Technology	VGA/SVGA
CONNECTIONS	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	HD15 (FEMALE)
PHYSICAL	
Color	White
Shipping Dimensions (hwd / in.)	5.20 x 5.20 x 0.91
Shipping Dimensions (hwd / cm)	13.21 x 13.21 x 2.31
Shipping Weight (lbs.)	0.10
Shipping Weight (kg)	0.05
ENVIRONMENTAL	
Operating Temperature Range	10 to 40 C (50 to 104 F)
Storage Temperature Range	-10 to 80 C (14 to 176 F)
Relative Humidity	Less than 85%, Non-Condensing
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.