

Universal Reversible USB 2.0 Adapter (Reversible A to Up Angle A M/F)

MODEL NUMBER: UR024-000-UP



Turn your standard USB cable into a Universal Cable

Description

The UR024-000-UP USB adapter (M/F) features a universal/reversible male end which allows the adapter to be plugged in any direction on a computer's USB port. Add this adapter to a standard USB cable, and convert it to a universal pluggable cable. The up-angle USB-A connector is ideal in situations where space is at a premium. USB 2.0 rated for 480 Mbps transfer rates. Fully molded with gold-plated contacts for a lifetime of use.

Features

- USB 2.0 Male-to Female adapter, with Universal / Reversible Male connector
- Male end can be plugged in any direction
- Up-Angle A connector ideal in situations where space is at a premium
- USB2.0 Hi-Speed rated

Highlights

- Universal / Reversible A-Male plugs in any direction
- Turns a standard USB cable into a Universal Cable
- Up-Angle A connector ideal in situations where space is at a premium
- USB2.0 Rated

Package Includes

- Universal Reversible USB 2.0 A-Male to Up-Angle A-Female Adapter

Specifications

OVERVIEW	
UPC Code	037332182920
Technology	USB 2.0 (High Speed)
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	REVERSIBLE USB A (MALE)
Side B - Connector 1	USB A (FEMALE)
Connector Style	Angled



Powering Business Worldwide



PHYSICAL	
Cable Jacket Color	Black
Cable Length (ft.)	0
Cable Length (m)	0.00
Shipping Dimensions (hwd / in.)	6.00 x 4.50 x 0.50
Shipping Dimensions (hwd / cm)	15.24 x 11.43 x 1.27
Shipping Weight (lbs.)	0.01
Unit Dimensions (hwd / in.)	6.000 x 4.500 x 0.500
ENVIRONMENTAL	
Operating Temperature Range	14° to 122°F (-10° to 50°C)
Storage Temperature Range	5° to 140°F (-15° to 60°C)
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 90% RH, Non-Condensing
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.