

A new hardware version (V2) was released in 2015 that requires a different Windows driver. Click the above Support tab to find old and new drivers and a file with instructions on how to determine which version you need.

USB-A to Serial Adapter Hub (DB9) - Keyspan, High-Speed (M/M), 4-Port

MODEL NUMBER: USA-49WG



Connect as many as four devices with a 9-pin serial port, such as modems, cellphones and scanners, to the USB Type-A port on your computer or laptop.

Description

The USA-49WG Keyspan® High-Speed 4-Port USB-to-DB9-Serial Adapter Hub allows you to connect as many as four 9-pin serial devices to a computer or laptop with a USB Type-A port. An easy and inexpensive way to add serial ports to your computer without hassle, the USA-49WG works with any DB9 serial device. Configuring and sharing data among multiple modems, GPS devices, cellphones, hand-held scanners, point-of-sale systems, touch screens, medical and scientific instruments, industrial process control devices and UPS systems is a breeze.

The included 6-foot cable supports data transfer speeds up to 460 Kbps—four times as fast as a built-in serial port. Five LEDs display port status at a glance. The USA-49WG requires no external power. Windows line monitor and data trace software included. Works with Windows (XP and later) and Mac OS X (10.6 through 10.13).

Features

Operate 4 DB9 Serial Devices Simultaneously

- Connects to networking equipment, modems, GPS devices, cellphones, hand-held scanners, point-of-sale systems, touch screens, medical and scientific instruments, industrial process control devices, UPS systems and other devices with a 9-pin serial port
- Supports data transfer speeds up to 460 Kbps—4 times as fast as a built-in serial port

Easy to Set Up and Use

Highlights

- Connects up to four DB9 serial devices to a computer USB-A port
- Supports data transfer speeds up to 460 Kbps
- Detachable 6-foot USB cable included
- No external power source required
- Works with Windows (XP and later) and Mac OS X (10.6 through 10.13)

System Requirements

- USB port
- Compatible with Windows 2000, XP, Vista, 7, 8, 8.1, 10, Server 2008 R2, Server 2012, Server 2012 R2, Server 2016
- Compatible with Mac OS X 10.6, 10.7, 10.8, 10.9, 10.10, 10.11, 10.12, 10.13

Package Includes

- USA-49WG USB-A to Serial Adapter Hub (DB9) - Keyspan, High-Speed (M/M), 4-Port
- USB cable, 6-ft. length
- CD with driver software and Owner's Manual



- No external power supply needed
- Includes detachable 6-ft. USB cable
- Can use with USB cable up to 16 ft. long
- 5 LEDs display port status at a glance

Compatible with Most Systems

- Works with Windows (XP and later) and Mac OS X (10.6 through 10.13)
- Includes Windows line monitor and data trace software

Specifications

OVERVIEW	
UPC Code	672603001441
PRODUCT OVERVIEW	
Product Overview	Keyspan-by-Tripp Lite 4-Port USB Serial Adapter
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	6.10 x 16.00 x 19.81
Shipping Dimensions (hwd / in.)	2.40 x 6.30 x 7.80
Shipping Weight (kg)	0.36
Shipping Weight (lbs.)	0.80
Unit Dimensions (hwd / cm)	4.57 x 15.24 x 7.62
Unit Dimensions (hwd / in.)	1.8 x 6 x 3
Unit Weight (kg)	0.16
Unit Weight (lbs.)	0.35
CONNECTIONS	
Side A - Connector 1	(4) DB9 (MALE)
FEATURES & SPECIFICATIONS	
Technology	Serial (RS232); USB
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>