

A new hardware version (V2) was released in 2015 that requires a different Windows driver. Click the above Support tab to find old and new drivers and a file with instructions on how to determine which version you need.

## USB-A to Serial Adapter Hub (DB9) - Keyspan, High-Speed (M/M), 4-Port

MODEL NUMBER: USA-49WG



Connect as many as four devices with a 9-pin serial port, such as modems, cellphones and scanners, to the USB Type-A port on your computer or laptop.

### Description

The USA-49WG Keyspan® High-Speed 4-Port USB-to-DB9-Serial Adapter Hub allows you to connect as many as four 9-pin serial devices to a computer or laptop with a USB Type-A port. An easy and inexpensive way to add serial ports to your computer without hassle, the USA-49WG works with any DB9 serial device. Configuring and sharing data among multiple modems, GPS devices, cellphones, hand-held scanners, point-of-sale systems, touch screens, medical and scientific instruments, industrial process control devices and UPS systems is a breeze.

The included 6-foot cable supports data transfer speeds up to 460 Kbps—four times as fast as a built-in serial port. Five LEDs display port status at a glance. The USA-49WG requires no external power. Windows line monitor and data trace software included. Works with Windows (XP and later) and Mac OS X (10.6 through 10.13).

### Features

#### Operate 4 DB9 Serial Devices Simultaneously

- Connects to networking equipment, modems, GPS devices, cellphones, hand-held scanners, point-of-sale systems, touch screens, medical and scientific instruments, industrial process control devices, UPS systems and other devices with a 9-pin serial port
- Supports data transfer speeds up to 460 Kbps—4 times as fast as a built-in serial port

### Easy to Set Up and Use

### Highlights

- Connects up to four DB9 serial devices to a computer USB-A port
- Supports data transfer speeds up to 460 Kbps
- Detachable 6-foot USB cable included
- No external power source required
- Works with Windows (XP and later) and Mac OS X (10.6 through 10.13)

### System Requirements

- USB port
- Compatible with Windows 2000, XP, Vista, 7, 8, 8.1, 10, Server 2008 R2, Server 2012, Server 2012 R2, Server 2016
- Compatible with Mac OS X 10.6, 10.7, 10.8, 10.9, 10.10, 10.11, 10.12, 10.13

### Package Includes

- USA-49WG USB-A to Serial Adapter Hub (DB9) - Keyspan, High-Speed (M/M), 4-Port
- USB cable, 6-ft. length
- CD with driver software and Owner's Manual



- No external power supply needed
- Includes detachable 6-ft. USB cable
- Can use with USB cable up to 16 ft. long
- 5 LEDs display port status at a glance

#### Compatible with Most Systems

- Works with Windows (XP and later) and Mac OS X (10.6 through 10.13)
- Includes Windows line monitor and data trace software

## Specifications

OVERVIEW	
UPC Code	672603001441
PRODUCT OVERVIEW	
Product Overview	Keyspan-by-Tripp Lite 4-Port USB Serial Adapter
PHYSICAL	
Shipping Dimensions (hwd / in.)	2.40 x 6.30 x 7.80
Shipping Dimensions (hwd / cm)	6.10 x 16.00 x 19.81
Shipping Weight (lbs.)	0.80
Shipping Weight (kg)	0.36
Unit Dimensions (hwd / in.)	1.8 x 6 x 3
Unit Dimensions (hwd / cm)	4.57 x 15.24 x 7.62
Unit Weight (lbs.)	0.35
Unit Weight (kg)	0.16
Color	Black
FEATURES & SPECIFICATIONS	
Technology	Serial (RS232); USB
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>