

WorkWise Desk-Mounted Workstation, Single Display

MODEL NUMBER: WWSS1332C



Clamps to your desk to make it an ergonomic sit-stand workstation without modifying the entire work surface.

Features

Enjoy the Benefits of Standing During Your WorkdayThis WorkWise™ sit-stand workstation clamps to the edge of a fixed-height table or desk, allowing you to enjoy the benefits of better workplace ergonomics. Standing for part of the day can help increase metabolism, improve alertness and productivity, reduce fatigue and decrease the risk of repetitive stress injuries. Ideal for home, school or office use, the WWSS1332C clamps to most fixed surfaces from one to 3.4 inches thick.

Easy to Adjust to Your Liking With a Single TouchJust one touch is all it takes to adjust your workstation's angles and heights to fit your comfort level. All sections move together for smooth transitions between sitting and standing modes. The full-motion arm revolves from -180° to +180° to give you plenty of flexibility in minimizing glare and providing comfortable viewing. It also rotates 360 degrees for viewing in portrait or landscape orientation. Increase or decrease tension using the included hex key to compensate for heavier or lighter loads.

Versatile Mounting Options Require Minimal Desk SpaceThis sit-stand workstation offers two different mounting methods: desk clamp or grommet mount. For easy and convenient installation and removal, use the desk clamp mounting option. For a permanent mounting solution, use the grommet mounting option. Necessary mounting hardware is included.

VESA-Compliant Mount Supports Up to 17.6 lb.The VESA-compliant single-arm mount fits most flat-panel monitors, televisions and other displays from 13 to 32 inches. It's compatible with 75 x 75 mm, 75 x 100 mm, 100 x 75 mm and 100 x 100 mm VESA mounting-hole patterns.

Extra-Large Keyboard Tray Holds the Most Popular ModelsThe large keyboard tray, with soft padded wrist rest, measures 26.2 x 10.2 inches and flips up to save space when not in use. A secondary surface is ideal for telephones, fans and other desk accessories.

5-Year Warranty and Environmentally Responsible DesignThe WWSS1332C sit-stand workstation comes with a 5-year warranty. It's manufactured in compliance with strict RoHS specifications.

Specifications

Highlights

- Clamps to fixed surface to leave valuable desk or table space clear
- Adjusts to fit wide range of flat-screen monitors from 13 to 32 in.
- Keyboard tray with padded wrist rest flips up when not in use to conserve workspace
- Monitor revolves from -180° to +180° and rotates 360° to customize the ideal viewing angle
- Includes necessary mounting hardware for immediate installation

Applications

- Transform your work area into a sit-stand environment to reap the health benefits of standing for part of your workday

Package Includes

- Bracket arm
- Support mast
- Keyboard shelf
- Clamp top
- Clamp bottom
- Cable clamp
- Grommet mount plate
- Pressure plate
- Wrench
- Hex key, 4 mm
- Hex key, 6 mm
- Mounting hardware
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

OVERVIEW	
UPC Code	037332212757
Device Compatibility	Monitor/HDTV; Computer; Laptop
PHYSICAL	
Color	Black; Silver
Material of Construction	Steel, Plastic
VESA Pattern (mm)	100x100; 100x75; 75x100; 75x75
Motion	Full Motion/Rotate
Mounting Location	Desk Clamp
Degrees of Motion	180 swivel and 360 rotate
Minimum Screen Size (in.)	13
Minimum Screen Size (cm)	33.02
Maximum Screen Size (in.)	32
Maximum Screen Size (cm)	81.28
Maximum Weight Capacity (lbs.)	17.6
Maximum Weight Capacity (kg)	8
Number of Displays	1
Unit Dimensions (hwd / in.)	26.200 x 45.300 x 40.200
Unit Dimensions (hwd / cm)	66.548 x 115.062 x 102.108
Unit Weight (lbs.)	25.7
Unit Weight (kg)	11.66
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Cord Management	No
Tools Necessary	Yes
Security Lock	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; RoHS3; CE (Europe); REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty



Powering Business Worldwide

TRIPP LITE
SERIES

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.