

MODEL:

# SR52UBDP

## SmartRack® 52U Deep Server Rack



52 Rack Units



3,000 lb.  
Stationary  
Load Capacity



2,250 lb.  
Rolling  
Load Capacity



Heavy-Duty  
Casters



Locking Doors &  
Side Panels



Standard  
19 in.  
Rack Width



Toolless  
Mounting Slots




Adjustable  
Rails with  
Easy-View  
Depth Index



Airflow  
Exceeds  
Server OEM  
Requirements



Integrated  
Baying Tabs



Square Hole  
Mounting

**A** Adjustable Mounting Rails (4)

**B** Adjustable PDU Mounting  
Rails with Toolless Mounting Slots  
(2 rails hold up to 4 vertical PDUs.)

**C** Roof Panel  
(Removable)

**D** Front Door  
(Lockable/Removable/Reversible)

**E** Split Rear Doors (2)  
(Lockable/Removable)

**F** Side Panels (4)  
(Lockable/Removable)


**G** Baying Tabs

**H** Heavy-Duty Casters (4)

**I** Heavy-Duty Levelers (4)

**J** Keys  
(For doors and side panels.)

Also Includes: Owner's manual, 2 shipping/  
stabilizing brackets and rack-mount equipment  
mounting hardware (50 cage nuts, 50 mounting  
screws, 50 nylon cup washers).



- Ships fully assembled for rapid deployment, but can be knocked down for easy reassembly in confined spaces
- Modular design optimized for quick configuration and reconfiguration
- Ideal for rack-mount server, network and telecom applications





**SEE NEXT PAGE FOR DETAILED UNIT MEASUREMENTS**

### Specifications

Model	SR52UBDP
Rack Spaces	52U
Stationary Load Capacity	3,000 lb. (1363 kg)
Rolling Load Capacity	2,250 lb. (1022 kg)
Unit Dimensions (H x W x D)	96 x 23.6 x 48.1 in. (2439 x 600 x 1222 mm)
Shipping Dimensions (H x W x D)	101.2 x 33.5 x 49.75 in. (2570 x 850 x 1264 mm)
Unit Weight	378.8 lb. (171.8 kg)
Shipping Weight	448.75 lb. (203.5 kg)
Certifications	UL 60950-1, RoHS, CE, IP20, EIA/ECA-310-E (Accommodates all standard 19-inch rack-mount equipment regardless of vendor.)







**TRIPP-LITE**  
by **EATON**



Dimensions: [mm] inches

Model:  
**SR52UBDP**  
**TRIPP-LITE**  
by **EAT•N**



OPTIONAL **SR**CABLETRAY AND **SR**CABLETRAYEXP CABLE MANAGEMENT ACCESSORIES SHOWN (MOUNTING POSITION ADJUSTS TO ACCOMMODATE A WIDE RANGE OF APPLICATIONS)

Model:  
**SR52UBDP**

**TRIPP-LITE**  
by **EATON**

1111 W. 35th Street  
Chicago, IL 60609 USA  
773.869.1234  
tripplite.com

Dimensions: [mm] inches

We have a policy of continuous improvement. Specifications are subject to change without notice.  
Photos and illustrations may differ slightly from actual products.

#### About Tripp Lite by Eaton

Tripp Lite joined the Eaton family in March 2021. Eaton has long been a premier name in backup power and power management. The acquisition of Tripp Lite transforms Eaton's distributed IT infrastructure and connectivity equipment capabilities. Combining our product strengths and expert personnel allows us to offer comprehensive and innovative solutions for critical power and digital infrastructure applications, backed by quality, service and support you can trust. Learn more at [tripplite.com/byEaton](https://tripplite.com/byEaton).