

Dual-Monitor Flex-Arm Desktop Clamp for 13" to 27" Displays

MODEL NUMBER: **DDR1327SDFC-1**



Desk clamp mounts your 13 to 27 in. monitors at a comfortable height to free up valuable space on your desk or work area.

Features

Rugged Steel Desk Clamp Lifts Your Monitors Above Your Work Area's Surface

This VESA-compliant desktop clamp mounts two flat-screen displays above your desk, table or workstation, allowing you to free up valuable surface space. Recommended for home or office use, the DDR1327SDFC-1 fits most flat-panel monitors from 13 to 27 inches. The clamp fits desktops ranging in thickness from 0.4 to 3.3 inches (10 to 85 millimeters). All hardware is included. Cable management brackets along the arms prevent excess cord clutter.

Swivel, Tilt and Rotate the Screens to Find the Most Comfortable Viewing Angles

The durable steel frame stands up to frequent adjustments, and the two flex arms support up to 17.6 pounds (8 kilograms) apiece. The flex arms adjust independently to optimize viewing angles, minimize glare and improve ergonomics. To minimize screen glare, reduce eye fatigue and increase viewing comfort, the DDR1327SDFC-1 features -30° to +30° tilt, -90° to +90° swivel and 360° rotation for positioning your screens.

VESA-Compliant Mounting Ensures Display Compatibility

VESA (Video Electronics Standards Association) promotes uniformity in the video electronics industry by developing standards for TVs and monitors. For hassle-free display compatibility, this monitor stand supports the following VESA mounting hole patterns: 75 x 75 and 100 x 100.

Highlights

- Steel frame clamps securely to your desk for mounting displays at comfortable levels
- -30° to +30° tilt, -90° to +90° swivel and 360° rotation help you find the perfect angle
- Dual flex arms adjust independently and support displays up to 17.6 lb. each
- Cable management brackets keep cords organized and help prevent excess clutter
- VESA compliance ensures compatibility with 75 x 75 and 100 x 100 mounting patterns

Package Includes

- DDR1327SDFC-1 Dual-Display Flex-Arm Desktop Clamp
- Mounting hardware
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332266118
Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Black



Powering Business Worldwide

TRIPP LITE
SERIES

Material of Construction	Steel
VESA Pattern (mm)	75x75; 100x100
Motion	Full
Mounting Location	Desk Clamp
Degrees of Motion	-30/+30 Tilt; 180 Swivel; 360 VESA head Rotate
Minimum Screen Size (in.)	13
Minimum Screen Size (cm)	33.02
Maximum Screen Size (in.)	27
Maximum Screen Size (cm)	68.58
Maximum Weight Capacity (lbs.)	17.6
Maximum Weight Capacity (kg)	8
Number of Displays	2
Unit Dimensions (hwd / in.)	19.600 x 34.900 x 4.900
Unit Dimensions (hwd / cm)	49.78 x 88.65 x 12.45
Unit Weight (lbs.)	8.3
Unit Weight (kg)	3.76
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Cord Management	Yes
Tools Necessary	Yes
Security Lock	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; RoHS3; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.