

Connection Requirement

This product is designed for use with computers with an HDMI port and is not intended to be used with Blu-Ray players, DVD players, or other HDMI devices.

HDMI to VGA with Audio Converter Cable Adapter for Ultrabook/Laptop/Desktop PC, (M/F), 6-in. (15.24 cm), TAA

MODEL NUMBER: P131-06N



Connect a PC, laptop or ultrabook with a HDMI port to a VGA display and speakers

Features

- Send audio/video from a PC, Laptop, Ultrabook or other computer with a HDMI output port to a VGA display and Mini Stereo speakers
- Supports video resolutions up to 1920x1200 (WUXGA)
- Supports 2-channel analog audio output
- Plug-and-Play
- No external power or drivers required
- Features a Micro USB port in the event that additional power is needed

Specifications

OVERVIEW	
UPC Code	037332180261
Product Type	Video Adapter
Device Compatibility	Chromebook; Computer; Laptop
Technology	HDMI; Stereo Audio; VGA/SVGA
CONNECTIONS	

Highlights

- Supports video resolutions up to 1920 x 1200 (WUXGA)
- Supports 3.5 mm. Mini Stereo Audio
- Supports 2-channel analog audio output
- No external power required
- Supports distances up to 100ft
- Plug-and-Play

System Requirements

- Computer with a HDMI output port
- VGA monitor or projector and 3.5 mm. Mini Stereo speakers
- This product is designed for use with computers (PC's, Laptops, Ultrabooks, etc.) with a HDMI port, and is not intended to be used with Blu-Ray players, DVD players, or other HDMI devices

Package Includes

- HDMI to VGA with Audio Converter Cable Adapter, 6 In.



Powering Business Worldwide

TRIPP LITE
SERIES

Side A - Connector 1	HDMI (MALE)
Side B - Connector 1	HD15 (FEMALE)
Side B - Connector 2	3.5MM (FEMALE)
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	0.5
Cable Length (m)	0.15
Cable Length (in.)	6
Cable Length (cm)	15.24
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.15
Shipping Weight (kg)	0.07
Unit Dimensions (hwd / in.)	9.000 x 7.000 x 0.500
Unit Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Unit Weight (lbs.)	0.15
Unit Weight (kg)	0.07
STANDARDS & COMPLIANCE	
Product Compliance	Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.