## SRX42UBDPWD / SRX42UBDPWDEXP

## SmartRack® Euro-Series Deep and Wide Rack Enclosure

**Rack Width** 



42 Rack Units



1360 ka

Stationary

1020 kg Rolling Load Capacity Load Capacity



Locking Doors & Heavy-Duty Casters **Side Panels** 





Standard Toolless 19-inch **Mounting Slots** (48.3 cm)



Adjustable Rails with Easy-View Depth Index



Airflow Meets or Exceeds Server OEM Requirements




Integrated **Baying Tabs** 



Square Hole Mounting

- A Adjustable Mounting Rails (4)
- **B** Adjustable PDU Mounting Rails with Toolless Mounting Slots (4)
- Roof Panel (Removable)
- Front Door (Lockable/Removable/Reversible)
- **E** Split Rear Doors (Lockable/Removable)
- F Side Panels (4) (Lockable/Removable; not included with SRX42UBDPWDEXP)
- G Heavy-Duty Casters (4)
- Heavy-Duty Levelers (4)
- (For doors and side panels.)

Also Includes: Owner's manual, 2 shipping/stabilizing brackets and rackmount equipment mounting hardware (50 cage nuts, 50 mounting screws, 50 nylon cup washers).




Specifications	Electronic Industries Alliance
Model	SRX42UBDPWD
Rack Spaces	42U
Stationary Load Capacity	1360 kg
Rolling Load Capacity	1020 kg
Unit Dimensions (H x W x D)	1994 x 800 x 1246 mm
Shipping Dimensions (H x W x D)	2119 x 850 x 1288 mm
Unit Weight	170 kg
Shipping Weight	192 kg
Certifications	UL 60950, IP20; EIA/ECA-310-E, ETSI,
	RoHS Compliant
Model	SRX42UBDPWDEXP
	(Identical to SRX42UBDPWD, but without side panels)
Unit Weight	129 kg
Shipping Weight	151 kg


- Enclosures ship fully assembled for rapid deployment, but can be knocked down for easy reassembly in confined spaces
- 1200 mm depth and 800 mm width allows extra space for cable management and hot-swap, removable power supplies
- Modular design optimized for quick configuration and reconfiguration
- Ideal for rack-mount server, network and telecom applications


## SEE NEXT PAGE FOR DETAILED UNIT MEASUREMENTS




1111 W. 35th Street Chicago, IL 60609 USA 773.869.1234 www.tripplite.com







DM VIEW TOP VIEW







MODELS:
SRX42UBDPWD
SRX42UBDPWDEXP



1111 W. 35th Street Chicago, IL 60609 USA 773.869.1234 www.tripplite.com

Dimensions: mm

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.