MODELS:

SRX47UBDPWD / SRX47UBDPWDEXP

SmartRack® Euro-Series Deep and Wide Rack Enclosure

47 Rack Units

1360 kg Stationary Load Capacity

1020 kg Rolling Load Capacity

Heavy-Duty Casters

Locking Doors & Side Panels

Standard 19-inch (48.3 cm) Rack Width

Toolless Mounting Slots

Adjustable Rails with Easy-View Depth Index

Airflow Meets or Exceeds Server OEM Requirements

Integrated Baying Tabs

Square Hole Mounting

- A Adjustable Mounting Rails (4)
- B Adjustable PDU Mounting Rails with Toolless Mounting Slots (4)
- C Roof Panel (Removable)
- D Front Door (Lockable/Removable/Reversible)
- E Split Rear Doors (Lockable/Removable)
- F Side Panels (4) (Lockable/Removable; not included with SRX47UBDPWDEXP)
- G Heavy-Duty Casters (4)
- H Heavy-Duty Levelers (4)
- I Keys (For doors and side panels.)

Also Includes: Owner's manual, 2 shipping/stabilizing brackets and rack-mount equipment mounting hardware (50 cage nuts, 50 mounting screws, 50 nylon cup washers).



- Enclosures ship fully assembled for rapid deployment, but can be knocked down for easy reassembly in confined spaces
- 1200 mm depth and 800 mm width allows extra space for cable management and hot-swap, removable power supplies
- Modular design optimized for quick configuration and reconfiguration
- Ideal for rack-mount server, network and telecom applications

SEE NEXT PAGE FOR DETAILED UNIT MEASUREMENTS

Specifications

Model	SRX47UBDPWD
Rack Spaces	47U
Stationary Load Capacity	1360 kg
Rolling Load Capacity	1020 kg
Unit Dimensions (H x W x D)	2215 x 800 x 1246 mm
Shipping Dimensions (H x W x D)	2469 x 850 x 1288 mm
Unit Weight	185 kg
Shipping Weight	207 kg
Certifications	UL 60950, IP20; EIA/ECA-310-E, ETSI, RoHS Compliant
Model	**SRX47UBDPWDEXP** (Identical to SRX47UBDPWD, but without side panels)
Unit Weight	140 kg
Shipping Weight	162 kg

TRIPP·LITE

1111 W. 35th Street
Chicago, IL 60609 USA
773.869.1234
www.tripplite.com







MODELS:

SRX47UBDPWD

SRX47UBDPWDEXP

TRIPP·LITE

Dimensions: mm

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.



BOTTOM VIEW



TOP VIEW



SIDE VIEW



REAR VIEW



FRONT VIEW

MODELS:

SRX47UBDPWD
SRX47UBDPWDEXP

TRIPP·LITE

1111 W. 35th Street
Chicago, IL 60609 USA
773.869.1234
www.tripplite.com

Dimensions: mm

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Copyright © 2019 Tripp Lite.