

MODEL:

PDUMH30HVATNET

Single-Phase Switched Rack-Mount ATS PDU



**High Voltage
Input/Output**



**Automatic
Transfer Switch**



**19 Switched
Outlets**



**5/5.8kW Load
Capacity**



**Network
Interface**




**2U Horizontal
Rack-Mount**



2 L6-30P Plugs

- A** Load Bank 1
- B** Load Bank 2
- C** L6-30R Outlet
- D** Cable Retention Brackets
- E** Primary Input Cord with L6-30P Plug
- F** Secondary Input Cord with L6-30P Plug
- G** Network Interface
- H** RJ45 Jack
- I** Manual Configuration Port
- J** ENVIROSENSE Port
- K** SNMP Reset Button
- L** Digital Load Meter
- M** Circuit Breaker – Bank 1
- N** Circuit Breaker – Bank 2
- O** Mounting Ears

Also Includes:
Owner's Manual, Cable Ties



- Distributes 5-5.8kW single-phase redundant power for devices with non-redundant power supply configurations
- Automatic transfer switching within 2-6ms
- Switched outlets and network interface supports individual outlet control on a real-time or programmable basis
- Digital load meter offers real-time output current monitoring

SEE NEXT PAGE FOR DETAILED UNIT MEASUREMENTS




1111 W. 35th Street
Chicago, IL 60609 USA
773.869.1234
www.tripplite.com


Specifications

Model	PDUMH30HVATNET
Voltage	208/240V (Single-Phase Input/Output)
Frequency	50/60 Hz
Load Capacity	5.8kW (240V), 5kW (208V)
Input Connector (x2)	NEMA L6-30P
Cord Length (x2)	10 ft. / 3 m
Outlets	19 (16 C13, 2 C19, 1 L6-30R)
Primary Mounting Option	2U Horizontal
Unit Dimensions	3.41 x 17.26 x 12.23 in. / 87 x 438 x 311 mm
Unit Weight	13.7 lb. / 6.2 kg
Standards	Tested to UL 60950-1 (US & Canada), NOM (Mexico), FCC Class A; RoHS; TAA






FRONT VIEW



SIDE VIEW



REAR VIEW

Dimensions: [mm] INCHES


Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

MODEL:
PDUMH30HVATNET



1111 W. 35th Street
Chicago, IL 60609 USA
773.869.1234

www.tripplite.com



TOP VIEW

Dimensions: [mm] INCHES

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

MODEL:
PDUMH30HVATNET



1111 W. 35th Street
 Chicago, IL 60609 USA
 773.869.1234
 www.tripplite.com