MODFI:

SR48UBEXPNDNR3

SmartRack® Heavy-Duty Open Frame Rack



48 Rack Units



3000 lb. Stationary Load Rating



3000 lb. Rolling Load Rating



3-Inch Heavy-Duty Casters



Accommodates Standard 19-inch



Toolless Mounting Slots



Adjustable Rails with Easy-View




Integrated Baying Tabs



Square Hole Mounting

- Adjustable Mounting Rails (4)
- B Adjustable PDU Mounting Rails with Toolless Mounting Slots (2 rails hold up to 4 vertical PDUs)
- 3-Inch Heavy-Duty Casters (4)
- D Heavy-Duty Levelers

Also Includes: Owner's manual, 2 stabilizing brackets and rackmount equipment mounting hardware (50 cage nuts, 50 mounting screws, 50 nylon cup washers)



Specifications	Electronic Industries Alliance
Model	SR48UBEXPNDNR3
Rack Spaces	48U
Stationary Load Capacity	3000 lb. (1361 kg)
Rolling Load Capacity	3000 lb. (1021 kg)
Unit Dimensions (H x W x D)	89 x 23.63 x 43 in. (2261 x 600 x 1092 mm)
Shipping Dimensions (H x W x D)	95 x 26 x 45 in. (2413 x 660 x 1143 mm)
Unit Weight	163 lb. (74 kg)
Shipping Weight	213 lb. (96.6 kg)
Standards	Tested to UL 60950, RoHS, CE, NOM,
	EIA/ECA-310-A, IEC 60297-3-100
Tripp Lite has a policy of continuous improv	vement. Specifications are subject to change without notice.


Also Available: Shock pallet models with special packaging to facilitate equipment pre-installation and reshipment to final site. Heavy-duty shock pallet holds up to 1250 lb. (568 kg), including the weight of the enclosure and pre-installed equipment. Add "SP1" to model numbers above to order shock pallet models.


- Enclosure ships fully assembled for rapid deployment, but can be knocked down for easy reassembly in confined spaces
- Does not include side panels to allow for baying of several racks in high-density applications
- Modular design optimized for quick configuration and reconfiguration
- · Ideal for rackmount server, network and telecom applications


SEE NEXT PAGE FOR DETAILED UNIT MEASUREMENTS




1111 W. 35th Street Chicago, IL 60609 USA 773.869.1234 www.tripplite.com









MODEL:
SR48UBEXPNDNR3



1111 W. 35th Street Chicago, IL 60609 USA 773.869.1234 www.tripplite.com

Dimensions: [mm] INCHES

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.